THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED. REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

**REVISIONS** REV. DESCRIPTIONS DATE **APPROVED** 1/12/02 CLASS A RELEASED 6/18/02 ADDED CAGE CODE

1. LARGE INSULATED ALLIGATOR CLIP w/4 mm SAFETY BANANA JACK.

2. SPECIFICATIONS:


INSULATOR: POLYAMIDE (NYLON) CONTACT: BRASS, NICKEL PLATÉD


3. RATING:

VOLTAGE: 1000 V CATIII/600 V CATIV (IEC61010-031)

CURRENT: 20 A MAX.

TEMPERATURE:  $-20^{\circ}$  C TO  $+80^{\circ}$  C.





-COLOR: 0 - BLACK


2 - RED

4 - YELLOW

5 - GREEN

6 - BLUE

9 - WHITE



THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	CONTRACT NO.			) - 1 T -	-4 Fl-		22020 Savi Panch Parkway		
		TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005				Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610					
			APPROVALS	DATE	TITLE	TITLE					
			DRAWN WDH	1/12/02		LARGE INSULATED ALLIGATOR CLIP					
			CHECKED		1						
			ENGR.	†	SIZE CAGE CODE			DWG. NO.	. 70040	REV.	
NEXT ASSY	USED ON		DESIGN ACTIVITY		Α	43F45		P2392A0		А	
APPLICATION					SCALE	1:1			SHEET 1 OF	1	

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Cal Test Electronics:

CT2401-6 CT2401-5 CT2401-0 CT2401-4 CT2401-2 CT2401-9 CT2489 CT3251-7 CT3251-1 CT3251-6 CT3251-5 CT3251-9 CT3251-2 CT3251-8 CT3251-4 CT3045 CT2392A-6 CT2392A-5 CT2392A-9 CT2392A-0 CT2392A-2 CT2490A CT3044-2 CT3044-0 CTM-48B2E CTM-26-9 CT3407-6 CTM-70S CTM-23-0 CT2845-5 CTM-40A-0 CTM-102BK-2 CTM-72-5 CT3438-2 CTM-25C CT3162-6 CTM-61 CTM-60HPR-6 CTM-49-9 CTM-651-0 CTM-29-0 CTM-75K CTM-25 CTM-90-5 CT3407-2 CT2487 CT2845-4 CT3218 CT3180-2 CTM-26-5 CTM-40A-2 CT2965-9 CTM-36-9 CT3438-9 CT3162-0 CT2592-3 CTM-65-2 CTM-72-2 CTM-13-4 CT3147-2 CTM-60HS-4 CTM-13-9 CTM-87-4 CT3180-3 CTM-63-9 CTM-60HS-5 CTM-47-9 CTM-47-6 CTM-31-9 CTM-27CG CT2592-9 CTM-11CPS CTM-70 CTM-60HPR-9 CT3189-6 CTM-30BL CTM-40C-0 CT3756 CTM-65-0 CT2400-6 CTM-35-9 CTM-32-4 CTM-78K CTM-70C CTM-60X CTM-31-4 CTM-102B-2 CT3441-9 CTM-72-6 CTM-5869-C CTM-5869-B CTM-32-2 CTM-11CPN CT3438-0 CTM-36-2 CTM-34 CT3148 CTM-30 CT2399-4 CTM-70CS