

# Shielded Ganged 1x2 RJ45

8P/8C Shielded Dual Port Tab-Up RJ45 Ethernet Connectors



## Product Features:


- Shielded RJ45 1x2 Connectors
- Minimum of 750 Mating Cycles
- Multiple Gold Contact Plating Options
- DWV - 1500VAC Contact to Shield
- Current Rating - 1.5A
- Voltage Rating - 125V
- UL94V-0 Flammability Rating

Part Number	Mechanical	Contact Gold Plating (min)	Latch Orientation	Operating Temp Range	LED Color (L/R)
HCJT2-802SK	A	6μ"	Tab-Up	-40°C to +85°C	None
HCJT2-804SK	A	30μ"	Tab-Up	-40°C to +85°C	None
HCJT2-805SK	A	50μ"	Tab-Up	-40°C to +85°C	None
HCJT2-802SK-L11	B	6μ"	Tab-Up	-40°C to +85°C	Green/Green
HCJT2-804SK-L11	B	30μ"	Tab-Up	-40°C to +85°C	Green/Green
HCJT2-805SK-L11	B	50μ"	Tab-Up	-40°C to +85°C	Green/Green
HCJT2-802SK-L12	B	6μ"	Tab-Up	-40°C to +85°C	Green/Yellow
HCJT2-804SK-L12	B	30μ"	Tab-Up	-40°C to +85°C	Green/Yellow
HCJT2-805SK-L12	B	50μ"	Tab-Up	-40°C to +85°C	Green/Yellow
HCJT2-802SK-L21	B	6μ"	Tab-Up	-40°C to +85°C	Yellow/Green
HCJT2-804SK-L21	B	30μ"	Tab-Up	-40°C to +85°C	Yellow/Green
HCJT2-805SK-L21	B	50μ"	Tab-Up	-40°C to +85°C	Yellow/Green

### Notes:




1. Alternate footprint variations available. Please contact the factory for additional information.
2. Part specific datasheets available upon request.

## Recommended Panel Cutout



# HALO 8P/8C Shielded Tab-Up 1x2 RJ45




## A - Mechanical (w/o LEDs)



Recommended PCB Layout (Top View)  
Dimensional Tolerance:  $\pm 0.08$  [0.003]

DIMENSIONS: mm [inch]  
TOLERANCE: .xx  $\pm 0.25$  [0.010]  
.x  $\pm 0.30$  [0.012]

## B - Mechanical (w/ LED's)



Recommended PCB Layout (Top View)  
Dimensional Tolerance:  $\pm 0.08$  [0.003]

DIMENSIONS: mm [inch]  
TOLERANCE: .xx  $\pm 0.25$  [0.010]  
.x  $\pm 0.30$  [0.012]



2880 Lakeside Drive #116  
Santa Clara, CA 95054  
(650) 903-3800  
[www.halo-electronics.com](http://www.halo-electronics.com)

HALO® Electronics is a leading supplier of high quality communication magnetics including signal transformers, filters, CMR chokes, PoE power transformers, DC/DC converters, and integrated Ethernet connectors. HALO's leading edge technology solutions are manufactured in ISO9001 and ISO14001 factories offering high quality products at a competitive price.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## HALO Electronics:

[HCJT2-802SK](#) [HCJT2-802SK-L11](#) [HCJT2-802SK-L12](#) [HCJT2-802SK-L21](#) [HCJT2-804SK](#) [HCJT2-805SK-L21](#)  
[HCJT2-804SK-L11](#) [HCJT2-804SK-L12](#) [HCJT2-804SK-L21](#) [HCJT2-805SK](#) [HCJT2-805SK-L11](#) [HCJT2-805SK-L12](#)  
[HCJT2-8041K-L12](#)