


10GBASE-T Transformer

SMD 10GBASE-T 24-Pin Single Port Isolation Modules

HALO
ELECTRONICS, INC.



Product Features:

- 10GBASE-T Ethernet Transformer/CMR Choke
- IEEE802.3an/af/at/bt Compliant Options
- 4PPoE - 4 Pair Power over Ethernet Available
- UL/EN60950 Recognized
- 100% Electrical Testing
- 1500Vrms Hi-Pot
- Patented Open Frame Construction

Part Number	Data Rate	Circuit	Total Power ¹	Current Per Pair	Operating Temp	Package	Max Height inch [mm]
TG10G-S100NJLF	10G	A	-	-	0 to 70°C	NJ	0.250 [6.35]
TG10G-S101NJLF	10G	B	-	-	0 to 70°C	NJ	0.250 [6.35]
TG10G-S102NJLF	10G	C	-	-	0 to 70°C	NJ	0.250 [6.35]
TG10G-RP02NJLF ²	10G	C	30W	350mA	0 to 70°C	NJ	0.250 [6.35]
TG10G-S12NZ5LF	10G	C	30W	350mA	0 to 70°C	NZ5	0.255 [6.48]
TG10G-E12NZ5LF	10G	C	30W	350mA	-40 to +85°C	NZ5	0.255 [6.48]
TG10G-HP6NZ5LF	10G	C	60W	600mA	0 to 70°C	NZ5	0.255 [6.48]
TG10G-HPE6NZ5LF	10G	C	60W	600mA	-40 to +85°C	NZ5	0.255 [6.48]
TG10G-HP10NZ5LF	10G	C	90W	1A	0 to 70°C	NZ5	0.255 [6.48]
TG10G-HPE10NZ5LF	10G	C	90W	1A	-40 to +85°C	NZ5	0.255 [6.48]

Notes:


¹ Power rating reduced to half when using only two pairs for power as in 802.3af/802.3at applications.

² Can be used in -40 to +85°C for non-PoE applications.


· Please contact the factory or representative for individual datasheets or additional information.

· Footprint interchangeable 2.5G/5G parts available at:
<https://www.haloelectronics.com/pdf/discrete-single-2G5G.pdf>


Circuit A



Circuit B




Circuit C




For additional information contact your [local representative](#), or HALO's support staff at (650) 903-3800 or info@haloelectronics.com

HALO 10GBASE-T Ethernet Transformers

Mechanical - NJ Package



Mechanical - NZ5 Package



Dimensions: inch [mm]
Co-Planarity: 0.004 [0.10]



2933 Bunker Hill Lane, #200
Santa Clara, CA 95054
(650) 903-3800
www.halo-electronics.com

HALO® Electronics is a leading supplier of high quality communication magnetics including signal transformers, filters, CMR chokes, PoE power transformers, DC/DC isolation modules, and integrated Ethernet connectors. HALO's high quality and competitively priced leading edge technology solutions are manufactured in ISO9001 and ISO14001 factories.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HALO Electronics:

[TG10G-S102NJRL](#) [TG10G-S100NJRL](#) [TG10G-S101NJRL](#) [TG10G-S101NJRLTR](#) [TG10G-S102NJRLTR](#) [TG10G-S100NJRLTR](#) [TG10G-RP02NJRL](#) [TG10G-RP02NJLF](#) [TG10G-S100NJLF](#) [TG10G-S100NJLFTR](#) [TG10G-RP02NJLFTR](#) [TG10G-S101NJLF](#) [TG10G-S101NJLFTR](#)