


Technical Data Sheet

Rosenberger

Cable assembly
RPC-1.00 Plug – RTK 047-F – RPC-1.00 Plug

L70-310-XXX



All dimensions are in mm; tolerances: $\pm 3\text{mm}$ for $A \leq 300\text{ mm}$; $\pm 1\%$ for $A > 300\text{ mm}$

Available variants

Type	max. Insertion loss	Weight (g) / pce
L70-310-XXX	$\leq 0.0020 * \sqrt{f[\text{GHz}]} + 0.00008 * f[\text{GHz}] \frac{\text{dB}}{\text{mm}}$	$0.070 \frac{\text{g}}{\text{mm}} * A[\text{mm}] + 8.9\text{g}$

XXX – length in mm = A

Maximum possible length = 6000mm

Note:

Weight:

First constant = Cable weight per mm; Second Constant = Connector left and Connector right weight per pce

Assembly parts

Connector left	RPC-1.00 Plug
Connector right	RPC-1.00 Plug
Cable	RTK 047-F
Armour	silicone rubber jacket over glass fiber braid / stainless steel spiral

Electrical data

Impedance	50 Ω
Frequency	DC to 110 GHz
Return loss ¹	$\geq 17\text{ dB}$, DC to 50 GHz
	$\geq 14\text{ dB}$, 50 to 110 GHz
Insertion loss ¹	see table available variants

Individual testing and documentation:

Measurement plot with all 4 S – Parameters (S11; S22; S21; S12) is included with the cable assembly and on the backside the care and handling instruction is printed.

¹ Return Loss and Insertion Loss includes the measurement adaptor

Mechanical data

Minimum bend radius	20.0 mm
---------------------	---------

Environmental data

Temperature range	- 40 °C to +125 °C
RoHS	compliant

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Marion Striegler	08.01.19	Markus Müller	30.10.19	b00	19-2041	Marion Striegler	30.10.19
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de						Tel. : +49 8684 18-0 Email : info@rosenberger.de	
							Page 1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[L70-310-140](#)