

## CHERRY KC 6000 SLIM



### Ultra-flat designer keyboard

The CHERRY KC 6000 SLIM keyboard impresses with its precise scissor mechanism, compact dimensions and state-of-the-art design. A sturdy keyboard with an integrated metal plate, it is a particularly attractive addition to the desk of the style-conscious user.

### Key Benefits

- Exceptionally compact, slim housing
- High-quality scissor mechanism for perfect keystroke
- Status LEDs for the CAPS LOCK, NUM and SCROLL keys
- 6 practical additional keys
- Sturdy construction with integrated metal plate

### Technical Data:

#### Layout (country or language):

(possible country/layout versions, others available on request)  
US English with EURO symbol

#### Housing Color:

Product dependant, see table "Models"

#### Key Color:

Product dependant, see table "Models"

#### Weight (product):

approx. 660 g / 1.46 lb

#### Total Weight (with packaging):

approx. 875 g / approx. 1.93 lb

#### Cable Length:

approx. 1.80 m / approx. 5.91 ft

#### Storage Temperature:

-20°C to 60°C / -4° F to 140° F

#### Operating Temperature:

0°C to 40°C / 32° F to 104° F

#### Current Consumption:

typ. 45 mA

#### Interface:

- USB

#### Product Approvals:

- cURus
- CE
- FCC



#### System Requirements:

- USB connection

#### Box Contents:

- CHERRY KC 6000 SLIM
- Operating instructions in hard copy

#### Dimensions (product):

approx. 440 x 130 x 15 mm / approx. 17.32 x 5.12 x .59 in

#### Packaging Dimensions:

approx. 453 x 170 x 33 mm / approx. 17.83 x 6.69 x 1.30 in

#### Keyboard:

- Key Technology: SX
- Service life, standard key: > 10 million key operations
- Inscription Technology: Laser
- Inscription Layout: Standard
- Number of Keys: 104+6

#### Packaging Unit:

- Number of products in the master package: 10
- Number of master packages per pallet: 20

#### Warranty:

2 years

Errors, technical changes and delivery delays may occur.  
Technical information refers only to the specifications of the products. Features may differ from the information provided.

## Models:

(possible country/layout versions, others available on request)

	Product Name	Order Number	EAN Code	Housing Color	Key Color
1	CHERRY KC 6000 SLIM	JK-1600EU-1	4025112088636	silver	white
2	CHERRY KC 6000 SLIM	JK-1600EU-2	4025112088568	black	black

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CHERRY:

[JK-1600EU-2](#)