

CHERRY MW 4500 LEFT

Wireless Ergonomic Mouse



Models may vary from the image shown

Ergonomic left-handed mouse in 45° design for relief of the wrist

Because the mouse is tilted at 45°, you do not need to place your hand completely flat on the CHERRY MW 4500. This results in a more natural hand position, which allows you to work without fatigue and with fewer problems with your wrist and tendons. This means repetitive strain injury can be avoided, or alleviated if you already have the symptoms. The click function of the right and left mouse button can be toggled at the touch of a button – without changing the system settings. The resolution can be adjusted with a button in 3 levels up to 1200 dpi for precise navigation and perfect adaptation to your preferences. Two additional thumb buttons allow you to jump to the next page or previous page in your Internet browser by touching a button. The extra small nano receiver can remain in your laptop without problems, or will find space on the bottom of the mouse. An all-rounder for the office or for home use!

Key Benefits

- Wireless mouse especially for left-handers
- Particularly ergonomic form in a 45° design
- Precise sensor with 3-level, adjustable resolution
- Status LED indicates low battery charge
- Right/left click function switchable at the touch of a button
- 6 buttons and a scroll wheel
- Feels pleasant in your hand due to abrasion-resistant surface finish
- Extra-small nano receiver

Technical Data:

Weight (product):

approx. 120 g/4.23 oz (mouse with battery)

Total Weight (with packaging):

approx. 220 g

Transmission Range:

approx. 10 m

Interface:

USB

Frequency Range:

2.400 GHz - 2.4835 GHz

Effective radiated power:

max. 10 mW (EIRP)

Current Consumption:

max. 5 mA (mouse), max. 35 mA (receiver)

Interface:

- USB

Product Approvals:

CE



FCC



System Requirements:

USB connection

Storage Temperature:

-15 °C to 60 °C

Operating Temperature:

0 °C to 40 °C

Box Contents:

- CHERRY MW 4500
- Operating instructions in hard copy
- 2 batteries (type AAA)
- 1 nano USB transmission receiver

Dimensions (product):

approx. 119 x 72 x 66 mm (mouse), approx. 19 x 15 x 6 mm (receiver)

Packaging Dimensions:

approx. 120 x 90 x 76 mm

Mouse:

- Scanning: Optical
- Resolution: 600 / 900 / 1200 dpi (adjustable)
- Number of Keys: 6
- Mouse Wheel Design: Scroll wheel with key function
- Design: Ergonomic, Left-handed design
- Connection: USB
- Housing Color: black
- Key Color: black

Packaging Unit:

- Number of products in the master package: 10
- Number of master packages per pallet: 156



CHERRY MW 4500 LEFT

Wireless Ergonomic Mouse

Warranty:

We put a lot of dedication and hard work into the development of our products and we are proud of their quality. This is why, in addition to the statutory guarantee mentioned in the operating instructions, we are granting an expanded manufacturer’s guarantee that is subject to the conditions stated below.

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free

of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery delays may occur. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

	Product Name	Order Number	EAN Code	Housing Color	Key Color
1	CHERRY MW 4500 LEFT	JW-4550	4025112090653	Black	Black

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CHERRY:

JW-4550