

Industrial

Keyboard Covers

Clear and Flexible



**Clear and Flexible
Keyboard Covers**

Main Applications

- HealthCare – easily disinfected & latex free
- Government/Military – durable construction
- Retail – POS compatible
- Consumer – 24/7 protection
- Industrial applications – Chemical resistant

Key Features

- Remains securely in place during use
- Protects against liquid spills, food, oil, dampness and dirt
- Flexible, transparent, durable
- Easily cleaned/disinfected in place
- Works with touchpad & card reader keyboards
- Custom made for a perfect fit
- Available for most keyboard models

Main Part Numbers

- **KBCV-11900W**
Plastic keyboard cover for all US layout G80-11900 models.
- **KBCV-14000W**
Plastic keyboard cover for all US layout G83-14xxx models with smart card reader.
- **KBCV-14100W**
Plastic keyboard cover for all US layout G83-14xxx models without smart card reader.
- **KBCV-1800N**
Plastic keyboard cover for all US layout G8x-1800 models without 'Windows keys'.
- **KBCV-1800W**
Plastic keyboard cover for all US layout G8x-1800 models with 'Windows keys'.
- **KBCV-4100N**
Plastic keyboard cover for all G84-4100 models without 'Windows keys'.
- **KBCV-4100W**
Plastic keyboard cover for all G84-4100 models with 'Windows keys'.
- **KBCV-4400**
Plastic keyboard cover for all US layout G84-4400 models.
- **KBCV-6100W**
Plastic keyboard cover for all G83-6104 models with 'Windows keys'.
- **KBCV-61401W**
Plastic keyboard cover for all G86-61401 models
- **KBCV-62401W**
Plastic keyboard cover for all G86-62401 models
- **KBCV-62410W**
Plastic keyboard cover for all G86-62410 models
- **KBCV-62411W**
Plastic keyboard cover for all G86-62411 models
- **KBCV-6700W**
Plastic keyboard cover for all G83-67xx models.
- **KBCV-7000W**
Plastic keyboard cover for all G81-7000 models with 2 & 3 track magnetic stripe reader.
- **KBCV-8000W**
Plastic keyboard cover for all G81-8000 models with 2 & 3 track magnetic stripe reader.
- **KBCV-8113W**
Plastic keyboard cover for all G80-8113 models.
- **KBCV-8200W**
Plastic keyboard cover for all G80-8200 models with 2 & 3-track magnetic stripe reader.

Additional product versions on request.

Industrial

Keyboard Covers

Clear and Flexible



Technical Data

Material

100% polyurethane w/ UV inhibitor

Maximum Service temperature

°F -60° to 200°

°C -53° to 93°

Thickness

10.5 mil

Easy Installation



- Gently lay cover over keyboard and align cover with the keys.



- Remove white Mylar from adhesive strips.



- Apply pressure to adhesive edge while smoothing out the cover.

Contact

Call, fax or visit our website for more information.

Last Update: 2/15/10

ZF Electronics Corporation

11200 88th Avenue
Pleasant Prairie, WI 53158

Phone: 262.942.6500
Web: www.cherrycorp.com

E-Mail: keyboardsupport@zf.com
Fax: 262.942.6566

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice.

Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2007 ZF Electronics Corporation



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CHERRY:

[KBCV-7000W](#) [KBCV-1800W](#) [KBCV-8000W](#) [KBCV62401W](#)