

Black and Pink ESD Foam, Lead Insertion Grade

Product Highlights

Closed Cell ESD Foam for IC leg and pin insertion.

Black ESD Foam: use for smaller more fragile pins.

Pink ESD Foam: use for larger more durable pins.

These rigid ESD Foams can also be used for blocking, bracing, cushioning and wrapping sensitive electronic devices.


RoHS 3 and REACH compliant

Specifications

Black ESD Foam: Crosslinked high-density polyethylene, rigid, closed-cell, carbon loaded, conductive, surface resistance 1×10^3 to 1×10^5 ohms/square.

Pink ESD Foam: Crosslinked high-density polyethylene, rigid, closed-cell, anti-static, electrostatic dissipative, surface resistance 1×10^9 to 1×10^{12} ohms/square.

Dimensional Tolerances: -2% / +4%



Orderable Part Numbers

Part Number	Color	Density (PCF)	Thickness	Length	Width
ESD-FOAM-BLACK-12X9X0.25	Black	2.8 lbs per cubic foot	0.25 inches	12 inches	9 inches
ESD-FOAM-BLACK-18X12X0.25	Black	2.8 lbs per cubic foot	0.25 inches	18 inches	12 inches
ESD-FOAM-BLACK-24X18X0.25	Black	2.8 lbs per cubic foot	0.25 inches	24 inches	18 inches
ESD-FOAM-BLACK-36X24X0.25	Black	2.8 lbs per cubic foot	0.25 inches	36 inches	24 inches
ESD-FOAM-BLACK-12X9X0.125	Black	2.8 lbs per cubic foot	0.125 inches	12 inches	9 inches
ESD-FOAM-BLACK-18X12X0.125	Black	2.8 lbs per cubic foot	0.125 inches	18 inches	12 inches
ESD-FOAM-BLACK-24X18X0.125	Black	2.8 lbs per cubic foot	0.125 inches	24 inches	18 inches
ESD-FOAM-BLACK-36X24X0.125	Black	2.8 lbs per cubic foot	0.125 inches	36 inches	24 inches
ESD-FOAM-PINK-12X9X0.5	Pink	2.1 lbs per cubic foot	0.5 inches	12 inches	9 inches
ESD-FOAM-PINK-18X12X0.5	Pink	2.1 lbs per cubic foot	0.5 inches	18 inches	12 inches
ESD-FOAM-PINK-24X18X0.5	Pink	2.1 lbs per cubic foot	0.5 inches	24 inches	18 inches
ESD-FOAM-PINK-36X24X0.5	Pink	2.1 lbs per cubic foot	0.5 inches	36 inches	24 inches
ESD-FOAM-PINK-12X9X0.25	Pink	2.1 lbs per cubic foot	0.25 inches	12 inches	9 inches
ESD-FOAM-PINK-18X12X0.25	Pink	2.1 lbs per cubic foot	0.25 inches	18 inches	12 inches
ESD-FOAM-PINK-24X18X0.25	Pink	2.1 lbs per cubic foot	0.25 inches	24 inches	18 inches
ESD-FOAM-PINK-36X24X0.25	Pink	2.1 lbs per cubic foot	0.25 inches	36 inches	24 inches
ESD-FOAM-PINK-12X9X0.125	Pink	2.1 lbs per cubic foot	0.125 inches	12 inches	9 inches
ESD-FOAM-PINK-18X12X0.125	Pink	2.1 lbs per cubic foot	0.125 inches	18 inches	12 inches
ESD-FOAM-PINK-24X18X0.125	Pink	2.1 lbs per cubic foot	0.125 inches	24 inches	18 inches
ESD-FOAM-PINK-36X24X0.125	Pink	2.1 lbs per cubic foot	0.125 inches	36 inches	24 inches

Product Photos



Black ESD Foam, Lead Insertion Grade



Pink ESD Foam, Lead Insertion Grade

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chip Quik:](#)

[ESD-FOAM-PINK-18X12X0.5](#)