


Cables and Connectors *HDMI / SATA HDD / Serial Cable*


	HDMI Cable	SATA HDD Cable	
			
Model Name	19B00-000403-00-RS	32801-000703-500-RS	32102-000100-200-RS
Cable Type	HDMI Cable	SATA HDD cable	SATA power cable
Connector	HDMI 90°	SATA 7-pin	4-pin + two 15-pin
Connector Type	HDMI	Lockable	SATA power connector
Length	35 cm	50 cm	15 cm


	SATA HDD Cable		
			
Model Name	32801-000201-300-RS	32801-000100-300-RS	32801-003706-100-RS
Cable Type	SATA + Power cable	SATA + Power cable	SATA + Power cable
Connector	SATA 7-pin + 2-pin wafer (P=2 mm)	SATA 7-pin + 4-pin wafer (P=2.54 mm)	SATA 7-pin + 4-pin
Connector Type	2-pin PH 2.0	4-pin PH 2.54 mm	
Length	SATA cable 15 cm Power cable 15 cm	SATA cable 20 cm Power cable 20 cm	SATA cable 20 cm Power cable 10 cm


	Serial cable		
			
Model Name	19800-000300-100-RS	19800-010900-200-RS	19800-020100-100-RS
Cable Type	Serial port cable	Serial port cable	Serial port cable
Board Side	10-pin (2x5) connector	10-pin (2x5) connector	2 x 10-pin (2x5) connector
Board Side Pitch	2.0 mm	2.54 mm	2.54 mm
Device Side	DE9M	DE9M	DE9M
Bracket	Yes	Yes	Yes
Length	30 cm	50 cm	23 cm

Part numbers listed in the product catalog are for reference purposes. IEI reserves the right to implement substitution parts when the function is not affected.

Cables and Connectors *Paralle / Serial Cable*

	Serial cable			
				
Model Name	19800-003600-200-RS	19800-000200-100-RS	32205-000702-200-RS	32205-002700-200-RS
Cable Type	Serial port cable	Serial port cable	Serial port cable	Serial port cable
Board Side	2 x 10-pin (2x5) connector	2 x 10-pin (2x5) connector	10-pin (2x5) connector	10-pin (2x5) connector
Board Side Pitch	2.54 mm	2.0 mm	2.54 mm	2.0 mm
Device Side	2 x DE9M	2 x DE9M	DE9M	DE9M
Bracket	Yes	Yes	No	No
Length	40 cm	30 cm	23 cm	20 cm

	Serial cable			
				 New
Model Name	32205-001203-200-RS	19800-026400-100-RS	32205-003800-300-RS	32005-003500-200-RS
Cable Type	Serial port cable	RS-232 & RS-422/485 cable	RS-422/485 cable	RS-232/422/485 cable
Board Side	40-pin (2x20) connector	14-pin (2x7) connector	4-pin (1x4) connector	1x 9pin (1x9) connector
Board Side Pitch	2.54 mm	2.0 mm	2.0 mm	1.25 mm
Device Side	4 x DE9M	2 x DE9M	DE9M	DE9M
Bracket	No	Yes	No	No
Length	40/40/40/40 cm	25 cm	20 cm	25 cm


	Paralle cable	
		
Model Name	19800-000049-RS	32223-000700-100-RS
Cable Type	Parallel port cable	Parallel port cable
Board Side	26-pin (2x13) connector	26-pin (2x13) connector
Board Side Pitch	2.54 mm	2.0 mm
Device Side	DB25F	DB25F
Bracket	Yes	No
Length	24 cm	28 cm

Part numbers listed in the product catalog are for reference purposes. IEI reserves the right to implement substitution parts when the function is not affected.

Cables and Connectors *USB / Power Cable / Keyboard / Mouse Cable*

	USB cable		
			
Model Name	32001-010800-200-RS	19800-000100-100-RS	CB-USB02-RS
Cable type	USB cable	USB cable	USB cable
Board side	2 x 4-pin connector	2 x 8-pin (2x4) connector	2 x 4-pin (1x4) connector
Board side pitch	2.54 mm	2.54 mm	2.54 mm
Device side	2 x USB	4 x USB	2 x USB
Bracket	No	Yes	Yes
Length	20 cm	30 cm	30 cm

	USB cable			
				
Model Name	CB-USB02A-RS	32001-002700-100-RS	32001-008600-200-RS	19800-010500-200-RS
Cable type	USB cable	USB cable	USB cable	USB 3.0 Front Panel cable
Board side	1 x 8-pin (2x4) connector	1 x 8-pin (2x4) connector	1 x 8-pin (2x4) connector	1 x 20-pin (2x10) connector
Board side pitch	2.0 mm	2.54 mm	2.0 mm	2.0 mm
Device side	2 x USB	2 x USB	2 x USB	2 x USB
Bracket	Yes	No	No	Yes
Length	30 cm	21 cm	21 cm	45 cm

	Power cable	Keyboard / Mouse cable		
				
Model Name	32100-087100-RS	19800-025700-100-RS	32006-000300-400-RS	32006-001100-201-RS
Cable type	12V power cable	Y-Cable	Y-Cable	Y-Cable
Board side	1 x 4-pin (2x2) connector	1 x 6-pin (1x6) connector	1 x male PS/2	1 x 6-pin (1x6) connector
Board side pitch		2.0 mm		2.0 mm
Device side	2 x 4-pin (1x4) molex	2 x Female PS/2	2 x Female PS/2	2 x Female PS/2
Bracket	No	Yes	No	No
Length	13 cm	22 cm	12 cm (KB) + 14 (MS)	13 cm

Part numbers listed in the product catalog are for reference purposes. IEI reserves the right to implement substitution parts when the function is not affected.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IEI:

[32102-000100-200-RS](#) [32205-003800-300-RS](#) [19800-000300-100-RS](#) [19800-020100-100-RS](#) [19800-000200-100-RS](#)