


Cables and Connectors *Paralle / Serial cable*

	Paralle cable				Serial cable
					
Model name	19800-000400-100-RS	19800-000142-00-RS	19800-000027-RS	32200-015100-RS	19800-000300-100-RS
Cable type	Parallel port cable	Parallel and serial port cable	Parallel and serial port cable	Parallel port cable	Single com port
Board side	26-pin (2x13) connector (2.54 mm)	26-pin (2x13) connector (2.54 mm) 10-pin (2x5) connector (2.54 mm)	26-pin (2x13) connector (2.0 mm) 10-pin (2x5) connector (2.0 mm)	26-pin (2x13) connector (2.0 mm)	10-pin (2x5) connector (2.0 mm)
Board side pitch	2.54 mm	2.54 mm	2.0 mm	2.0 mm	2.0 mm
Device side	DB25F	DB25F + DE9M	DB25F + DE9M	DB25F	2.0 mm
Bracket	Yes	Yes	Yes	No	YES
Length	24 cm	24 cm	24 cm	28 cm	30cm

	Serial cable					
						
Model name	19800-000114-RS	19800-000047-RS	19800-000051-RS	19800-000113-RS	19800-000112-RS	32200-000015-RS
Cable type	Single com port	Serial port cable	Serial port cable	Serial port cable	Serial port cable	Serial port cable
Board side	10-pin (2x5) connector (2.54 mm)	10-pin (2x5) connector (2.54 mm)	2 x 10-pin (2x5) connector (2.54 mm)	2 x 10-pin (2x5) connector (2.54mm)	2 x 10-pin (2x5) connector (2.0 mm)	10-pin (2x5) connector (2.54 mm)
Board side pitch	2.54 mm	2.54 mm	2.54 mm	2.54 mm	2.0 mm	2.54 mm
Device side	DE9M	DE9M	2 x DE9M	2 x DE9M	2 x DE9M	DE9M
Bracket	Yes	Yes	Yes	Yes	Yes	No
Length	50 cm	30 cm	23 cm	40 cm	30 cm	23 cm

	Serial cable					
						
Model name	32200-000049-RS	32205-001203-100-RS	32100-147900-RS	32200-025401-RS	32200-026800-RS	19800-000058-RS
Cable type	Serial port cable	4 x com port	Serial port cable	Serial port cable	RS-422/485 cable	RS-232 & RS-422/485 cable
Board side	10-pin (2x5) connector (2.0 mm)	40-pin (2x20) connector (2.54 mm)	40-pin (2x20) connector (2.0 mm)	40-pin (2x20) connector (2.0 mm)	16-pin (2x8) connector (2.54 mm)	14-pin (2x7) connector (2.54 mm)
Board side pitch	2.0 mm	2.54 mm	2.0 mm	2.0 mm	2.54 mm	2.54 mm
Device side	DE9M	4 x DE9M	4 x DE9M	4 x DE9M	4 x DE9M	2 x DE9M
Bracket	No	No	No	No	No	Yes
Length	20 cm	40/40/40/40 cm	30 cm	30 cm	12 cm	25.5 cm

	Serial cable				
					
Model name	19800-000110-RS	32205-000300-100-RS	32200-000061-RS	19800-000063-RS	32200-074800-RS
Cable type	RS-232 & RS-422/485 cable	RS-232 & RS-422/485 cable	RS-232 & RS-422/485 cable	RS-232 & RS-422/485 cable	RS-422/485 cable
Board side	14-pin (2x7) connector (2.0 mm)	14-pin (2x7) connector (2.0 mm)	14-pin (2x7) connector (2.0 mm)	4-pin (1x4) connector (2.54 mm)	4-pin (1x4) connector (2.0 mm)
Board side pitch	2.0 mm	2.0 mm	2.0 mm	2.54 mm	2.0 mm
Device side	2 x DE9M	2 x DE9M	2 x DE9M	DE9M	DE9M
Bracket	Yes	No	No	No	No
Length	25 cm	29 cm	23 cm	40 cm	20 cm

Part numbers listed in the product catalog are for reference purposes. IEI reserves the right to implement substitution parts when the function is not affected.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IEI:

[19800-000110-RS](#) [19800-000027-RS](#)