


PAC-700G 7-slot Half-size Compact Chassis



CD-ROM, and HDD are not included in package.



Easy hot-replaceable fan



Step 1:
Loosen the thumb screws



Step 2:
Pull the fan out gently



Step 3:
Unplug the power connector


Features

- ◆ RoHS compliant design
- ◆ Two USB ports on the front panel
- ◆ One, 8 cm cooling fan with fan filter
- ◆ Easy access design for quick fan replacement
- ◆ Lockable door prevents unauthorized access

Specifications

◆ Construction	Heavy duty metal
◆ SBC Form Factor	Half-size, slot CPU card
◆ Drive Combinations	2 x 5.25" + 1 x front accessible 3.5"
	or 1 x 5.25" + 2 x front accessible 3.5"
	or 1 x 5.25" + 1 x front accessible 3.5" + 1 x 3.5" HDD
◆ Cooling Fans	1 x 8cm
◆ I/O Ports	2 x USB on front panel
◆ I/O Openings	2 x LPT, 2 x COM
◆ Expansion Slots	7 slots
◆ Indicators	Power, HDD
◆ Buttons	power switch, reset
◆ Operating Temperature	0°C~50°C
◆ Operation Humidity	10% ~ 90%
◆ Color	B: Black
◆ Weight (Net/Gross)	6.2 kg / 9 kg
◆ Dimensions (DxWxH)	279 mm x 321 mm x 176 mm

Dimensions (measurement units: millimeter)



Backplane Options

Model No.	SBC Type	PCI	ISA	PCIe			PSU Connector
				x1	x4	x16	
BP-7S-RS	ISA	0	7	0	0	0	AT
IP-7S-RS	PCISA	4	2	0	0	0	AT
IP-7SA-RS	PCISA	4	2	0	0	0	ATX
HPE-7S1	PCI/PIC0e	4	0	2	0	0	ATX

Ordering Information

Part No.	Description
PAC-700GB-R11/BP-7S/916AP	7-slot Half-size chassis, with BP-7S-RS-R30 and ACE-916AP-RS
PAC-700GB-R11/IP-7S/916AP	7-slot Half-size chassis, with IP-7S-RS-R30 and ACE-916AP-RS
PAC-700GB-R11/A618A	7-Slot Half-size Compact Chassis, Black, 1 x 8cm fan, with ACE-A618A-RS-R11 (180W ATX model), RoHS

Power Supply Options

Type	Model No.	Watt
AT	ACE-916AP-RS	150W
ATX	ACE-A618A-RS-R11	180W
	ACE-A225A-RS	250W

PAC-700G can support single 1U height PSU. For more models of IEI PSU, please refer to section 7 or visit www.ieiworld.com.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IEI:

[PAC-700GB-R11/A618A](#) [PAC-700GB-R11/BP-7S/916AP](#) [PAC-700GB-R11/A618C](#)