

PuIM-1G4T-I211


Intel® Ethernet Controller I211 based Network Interface Card with 4 x 1GbE RJ-45 by 4 PCIe 2.0 x2 Interface



Features

- 1 x Intel® Ethernet Controller I211-AT
- 4 ports RJ-45 connector
- 4 x PCIe 2.0 x2
- Optional LAN Bypass
- RoHS compliant

Dimensions (Unit: mm)



Model Name	PuIM-1G4T-I211	PuIM-1G4T-I211-BP
Form Factor	IEI Networking Module - PuIM	
NIC	Intel® Ethernet Controller I211-AT	
LAN Bypass	No	YES, two pairs
LAN Interface	1 GbE RJ-45	
Ports	4	
Host Interface	4 x PCIe 2.0 x2	
Operating Temp	0 ~ 40°C	
Humidity	5% ~ 90% RH, Non-condensing	
Dimensions (mm)	165.50 (L) x 77.8 (W) x 44.2 (H)	

Packing List


1 x PuIM-1G4T-I211 or PuIM-1G4T-I211-BP module
1 x L-shaped T10 Plum Wrench 1 x QIG

Ordering Information

Part No.	Description
PuIM-1G4T-I211-R10	Intel® Ethernet Controller I211 based Network Interface Card with 4 x 1GbE RJ-45 w/o by pass 4 PCIe 2.0 x2 Interface
PuIM-1G4T-I211-BP-R10	Intel® Ethernet Controller I211 based Network Interface Card with 4 x 1GbE RJ-45 4 PCIe 2.0 x2 Interface with by pass function

PuIM Network Module Slot

- IEI PuIM Network Module slots support 8 lanes of PCIe Gen3 signal which is form CPU and PCH
- Support smart NIC via PuIM Network Module



Slot/PCIe Signals	A (One PCIe x8 + Two PCIe x4)		B (Two PCIe x4 + Four PCIe x2)	
Supported Networking Module	PuIM-10G4SF-XL710 PuIM-10G4SF-XL710-BP	PuIM-10G4SF-MLX PuIM-25G2SF-MLX	PuIM-1G4T-I211 PuIM-1G4T-I211-BP PuIM-1G8T-BCM5720	PuIM-10G4SF-MLX PuIM-10G4T-AQC107
Compatible Model	PUZZLE-IN001 PUZZLE-IN004	PUZZLE-A001	PUZZLE-IN001 PUZZLE-IN001A	



IEI Integration Corp.

No. 29, Zhongxing Rd, Xizhi Dist., New Taipei City 221, Taiwan
TEL: +886-2-8691-6798 / +886-2-2690-2098
sales@ieiworld.com www.ieiworld.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IEI:

[PuIM-1G4T-I211-BP-R10](#) [PuIM-1G4T-I211-R10](#)