

VIA
ALTA DS 3

High-performance Edge AI system with dual 4K screen support and rich wireless and I/O connectivity options

Features

- Qualcomm® Snapdragon™ 820E Embedded Platform
- Supports dual 4K display resolution
- Features Qualcomm® Neural Processing SDK support
- Wi-Fi & Bluetooth 4.1 or 4G LTE wireless connectivity options
- Dual display mirror & independent video playback modes available




Specifications


Model Name	ALTA DS 3
Processor	Qualcomm® Snapdragon™ 820E Embedded Platform - Two high-performance Kryo cores up to 2.15GHz - Two low power Kryo cores up to 1.593GHz
System Memory	4GB POP LPDDR4 RAM
Storage	16GB eMMC flash memory M.2 slot for M.2 2280 NVMe SSD (PCIe 1 Lane) SD card slot
Graphics	Qualcomm® Adreno™ 530 GPU 3D graphics accelerator with 64-bit addressing 624MHz Graphics engine supporting OpenGL ES 3.1/GEP, GL4.4, DX11.3/4, OpenCL 2.0, Renderscript-Next Supports H.264, H.265 (HEVC 8/10-bit) video decoding up to: 4K@60fps
Trusted Platform Module	TPM1.2 : ST33TPM1212C
Wireless Connectivity	NFA324A-12H32 QCA6174A-1 Wi-Fi 802.11 a/b/g/n/ac + BT 4.1 combo LGA module with 2 antenna connectors
Audio	WCD9335 Audio Codec
HDMI	Integrated HDMI 2.0 transmitter and dual DSI to HDMI 1.4 converter
Expansion I/O	1 miniPCIe slot (USB only) 1 SIM card slot
Front Panel I/O	2 USB 3.0 ports 1 SD card slot 2 Audio jacks: Line-out and Mic-in 1 Power Button with blue power LED
Back Panel I/O	2 HDMI ports 1 USB 3.0 port 1 Mini USB 2.0 port (fastboot mode only) 1 Gigabit Ethernet Port 1 Antenna hole 1 DC-in jack
Power Supply	12V DC-in
Operating System	Android 8.0
Operating Temperature	0°C ~ 40°C
Operating Humidity	0% ~ 95% @ 40°C (non-condensing)
Storage Temperature	-20°C~ 70°C
Mechanical Construction	Plastic frame Metal bracket
Mounting	Stand holder, VESA mount (optional)
Dimensions	175mm(W) x 25mm(H) x118mm(D) (6.88" x 0.98" x 4.64")
Weight	0.61kg (1.34lbs)
Compliance	BSMI, CE, FCC



Front Panel External I/O



Back Panel External I/O




Ordering Information

Part Number	SoC Frequency	Description
ALTADS30VA001-T (US Only)	Qualcomm® Snapdragon™ 820E Embedded Platform @ 2.15GHz/1.593GHz	Android system with 2.15GHz Qualcomm® Snapdragon™ 820E Embedded Platform, 16GB eMMC, 4GB POP LPDDR4 RAM, 2 HDMI, 3 USB 3.0, Mini USB 2.0, Gigabit Ethernet, Wi-Fi, Bluetooth 4.1, SD card slot, M.2 slot, SIM card slot, miniPCle slot, Stand holder, US power cord, 12V DC-in
ALTADS30VA002-T	Qualcomm® Snapdragon™ 820E Embedded Platform @ 2.15GHz/1.593GHz	Android system with 2.15GHz Qualcomm® Snapdragon™ 820E Embedded Platform, 16GB eMMC, 4GB POP LPDDR4 RAM, 2 HDMI, 3 USB 3.0, Mini USB 2.0, Gigabit Ethernet, SD card slot, M.2 slot, SIM card slot, miniPCle slot, Stand holder, US power cord, 12V DC-in

Optional Accessories

Wireless Accessories	
Part Number	Description
EMIO-2573-00A0	Quectel EC25-A 4G/LTE mobile broadband full size miniPCle module for USA with assembly kit and antenna pack
Mounting Options	
Part Number	Description
VT6076-C0000A1	VESA mount cradle

Dimensions



Packing List

Items
ALTA DS 3 system
Stand holder
AC-to-DC adapter
USA Power cord
Wi-Fi antenna

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[VIA Technologies:](#)

[ALTADS30VA001-T](#)