







used for: D-SUB

9 way

15 - 50 way



Metal screw with plastic head



| No. of pos. | A     | B    | C     | D    | ØE   | Part no:   |
|-------------|-------|------|-------|------|------|------------|
| 9           | 31.30 | 25.0 | 35.15 | 15.0 | 8.0  | 165X11759X |
| 15          | 39.62 | 33.3 | 39.15 | 15.0 | 9.0  | 165X11769X |
| 25          | 53.52 | 47.0 | 39.15 | 15.0 | 11.0 | 165X11779X |
| 37          | 69.80 | 63.5 | 39.15 | 15.0 | 11.0 | 165X11789X |
| 50          | 67.41 | 61.1 | 39.15 | 19.0 | 14.5 | 165X11799X |



THIS DRAWING MAY NOT BE COPIED OR  
REPRODUCED IN ANY WAY, AND MAY NOT  
BE PASSED ON TO A THIRD PARTY WITHOUT  
WRITTEN PERMISSION.  
OWNERSHIP AND COPYRIGHT OF CONEC GmbH  
DO NOT ALTER CAD DRAWING BY HAND

| rev. | description | date | name |
|------|-------------|------|------|
|      |             |      |      |
|      |             |      |      |
|      |             |      |      |
|      |             |      |      |
|      |             |      |      |
|      |             |      |      |
|      |             |      |      |
|      |             |      |      |
|      |             |      |      |

|                                                                                     |           |                                                                                       |
|-------------------------------------------------------------------------------------|-----------|---------------------------------------------------------------------------------------|
| tolerance                                                                           |           |  |
| 2002                                                                                | date      | name                                                                                  |
| drawn                                                                               | 29.01.    | Parei                                                                                 |
| appd.                                                                               | 30.01.    | E. Mickenbecker                                                                       |
| norm                                                                                | DIN 41652 |                                                                                       |
| d-old                                                                               | KAT113AA  |                                                                                       |
|  |           |                                                                                       |

|           |                                                                     |       |   |
|-----------|---------------------------------------------------------------------|-------|---|
| scale:    | 1:1                                                                 |       |   |
| material: | Polycarbonat + GF black                                             |       |   |
| title:    | Plastic Hood<br>with side cable exit<br>with shielding, 9 - 50 pos. |       |   |
| dwg no:   | AutoCAD 2000                                                        | DIN-A | 3 |
| part no:  | SEE TABLE                                                           |       |   |
| sh:       | 1/1                                                                 |       |   |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[165X11769X](#)