

ACCESSORIES




ACCESSORIES

Tools

Hand crimp tool	Suitable contacts	Part No.
	Suitable for: M8 P-coding field-attachable Data contacts B12/B17/B23 Power contacts B12/B17	36-000640
Insert for hand crimp tool		
	Suitable for: M8 P-coding field-attachable Data contacts B12/B17/B23 Power contacts B12/B17	36-000610

ACCESSORIES

Hybrid cables

GAZ= Hybrid cable, halogenfree, for drag chain applications							Datasheet No.
	Wire cross section power	Wire cross section data	Number of wires power	Number of wires data	Color cable jacket	Wire colors power	Wire colors data
	0.75 mm²	AWG22	2	4	black	WT - RD - BU - OR - BU	781-GAZ010H
	1.5 mm²	AWG22	3	4	black	BN - WT - BU - YE - GN/ OR - YE BU	781-GAZ011H
	2.5 mm²	AWG22	3	4	black	BN - WT - BU - YE - GN/ OR - YE BU	781-GAZ012H
	1.5 mm²	AWG22	4	4	black	BN - WT - BK - YE - GY - OR - GN/ BU YE	781-GAZ013H
	1.5 mm²	AWG22	5	4	black	BN - WT - BU - YE - GY - OR - BK - BU GN/ YE	781-GAZ014H

ACCESSORIES


Color coding

Connectors overmoulded/Panel mount connectors male, square housing	Size	Color	Part No.
	B12	yellow	56-99000
	B12	green	56-99001
	B17	yellow	57-99000
	B17	green	57-99001
	B17	orange	57-99002
Connectors field attachable			
	B12	yellow	56-99002
	B12	green	56-99003
	B17	yellow	57-99003
	B17	green	57-99004
	B17	orange	57-99005
Panel mount connector male, front- and back panel mounting			
	B12	yellow	56-99004
	B12	green	56-99005
	B17	yellow	57-99006
	B17	green	57-99007
	B17	orange	57-99008

ACCESSORIES

Protection caps

Receptacle male



Size B12

Size B17

Material protection cap

Degree of protection

Color

Part No.

✓

PA

IP67

black

56-99006

✓


PA

IP67

black

57-99010

Female connector (overmoulded, field attachable)



✓

PA

IP67

black

56-99008

✓

PA


IP67

black

57-99012

ACCESSORIES

Hex nut



Size B12

Size B17

Thread

Width across flats

Outer Ø = D [mm]

Height = H [mm]

Material

Description

Part No.

✓

M18x1

SW24

26

5

CuZn, Ni

56-99010

✓

M24x1

SW30

32

5

CuZn, Ni

57-99014

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[56-99002](#) [56-99005](#) [57-99007](#) [56-99003](#) [56-99010](#) [57-99003](#) [56-99000](#) [57-99008](#) [57-99006](#) [57-99005](#) [56-99004](#)
[56-99006](#) [57-99004](#) [56-99008](#) [57-99012](#) [57-99010](#) [56-99001](#)