


Π-FILTER D-SUB ADAPTER

Socket connector / Plug connector – Precision machined contacts – Full Metal




RoHS compliant – CSA listed, File No.: LR 115000-1 – UL listed, File No.: E202784

DESCRIPTION

- Mounting styles:
 - with 4-40 UNC or M3 jack screw
 - with 4-40 UNC or M3 hex bolt
- Quality class 3 (also available in quality class 1)
- Shell: Steel tin plated


PRODUCT DRAWING

Version with jack screw



No. of pos.	A -0.76	B1 -0.25	B2 +0.25	C	D -0.3
09	31.19	16.46	16.79	25.00 $+0.12/-0.13$	6.10
15	39.52	24.79	25.12	33.30 $+0.15/-0.10$	6.12
25	53.42	38.50	38.84	47.04 $+0.13/-0.10$	5.99
37	69.70	54.96	55.30	63.50 $+0.13/-0.10$	5.99

Version with hex bolt



ORDER DATA

Capacitance 2 x 180 pF					
Socket Connector / Plug Connector with Jack Screw			Socket Connector / Plug Connector with Hex Bolt		
No. of pos.	Mounting style	Part Number	No. of pos.	Mounting style	Part Number
09	4-40 UNC Jack screw	MAP 1XAAAR02R361 X	09	4-40 UNC Hex bolt	MAP 1XAAAH02R361 X
15	4-40 UNC Jack screw	MAP 2XAAAR02R361 X	15	4-40 UNC Hex bolt	MAP 2XAAAH02R361 X
25	4-40 UNC Jack screw	MAP 3XAAAR02R361 X	25	4-40 UNC Hex bolt	MAP 3XAAAH02R361 X
37	4-40 UNC Jack screw	MAP 4XAAAR02R361 X	37	4-40 UNC Hex bolt	MAP 4XAAAH02R361 X
09	M3 Jack screw	MAP 1XAAAR01R361 X	09	M3 Hex bolt	MAP 1XAAAH01R361 X
15	M3 Jack screw	MAP 2XAAAR01R361 X	15	M3 Hex bolt	MAP 2XAAAH01R361 X
25	M3 Jack screw	MAP 3XAAAR01R361 X	25	M3 Hex bolt	MAP 3XAAAH01R361 X
37	M3 Jack screw	MAP 4XAAAR01R361 X	37	M3 Hex bolt	MAP 4XAAAH01R361 X

π -FILTER D-SUB ADAPTER

Socket connector / Plug connector – Precision machined contacts – Full Metal

ORDER DATA

Capacitance 2 x 370 pF

SOCKET CONNECTOR / PLUG CONNECTOR WITH JACK SCREW

No. of pos.	Mounting style	Part Number
09	4-40 UNC Jack screw	MAP 1XAAAR02R741 X
15	4-40 UNC Jack screw	MAP 2XAAAR02R741 X
25	4-40 UNC Jack screw	MAP 3XAAAR02R741 X
37	4-40 UNC Jack screw	MAP 4XAAAR02R741 X
09	M3 Jack screw	MAP 1XAAAR01R741 X
15	M3 Jack screw	MAP 2XAAAR01R741 X
25	M3 Jack screw	MAP 3XAAAR01R741 X
37	M3 Jack screw	MAP 4XAAAR01R741 X

SOCKET CONNECTOR / PLUG CONNECTOR WITH HEX BOLT

No. of pos.	Mounting style	Part Number
09	4-40 UNC Hex bolt	MAP 1XAAAH02R741 X
15	4-40 UNC Hex bolt	MAP 2XAAAH02R741 X
25	4-40 UNC Hex bolt	MAP 3XAAAH02R741 X
37	4-40 UNC Hex bolt	MAP 4XAAAH02R741 X
09	M3 Hex bolt	MAP 1XAAAH01R741 X
15	M3 Hex bolt	MAP 2XAAAH01R741 X
25	M3 Hex bolt	MAP 3XAAAH01R741 X
37	M3 Hex bolt	MAP 4XAAAH01R741 X

Capacitance 2 x 830 pF

SOCKET CONNECTOR / PLUG CONNECTOR WITH JACK SCREW

No. of pos.	Mounting style	Part Number
09	4-40 UNC Jack screw	MAP 1XAAAR02R162 X
15	4-40 UNC Jack screw	MAP 2XAAAR02R162 X
25	4-40 UNC Jack screw	MAP 3XAAAR02R162 X
37	4-40 UNC Jack screw	MAP 4XAAAR02R162 X
09	M3 Jack screw	MAP 1XAAAR01R162 X
15	M3 Jack screw	MAP 2XAAAR01R162 X
25	M3 Jack screw	MAP 3XAAAR01R162 X
37	M3 Jack screw	MAP 4XAAAR01R162 X

SOCKET CONNECTOR / PLUG CONNECTOR WITH HEX BOLT

No. of pos.	Mounting style	Part Number
09	4-40 UNC Hex bolt	MAP 1XAAAH02R162 X
15	4-40 UNC Hex bolt	MAP 2XAAAH02R162 X
25	4-40 UNC Hex bolt	MAP 3XAAAH02R162 X
37	4-40 UNC Hex bolt	MAP 4XAAAH02R162 X
09	M3 Hex bolt	MAP 1XAAAH01R162 X
15	M3 Hex bolt	MAP 2XAAAH01R162 X
25	M3 Hex bolt	MAP 3XAAAH01R162 X
37	M3 Hex bolt	MAP 4XAAAH01R162 X

Capacitance 2 x 1300 pF

SOCKET CONNECTOR / PLUG CONNECTOR WITH JACK SCREW

No. of pos.	Mounting style	Part Number
09	4-40 UNC Jack screw	MAP 1XAAAR02R262 X
15	4-40 UNC Jack screw	MAP 2XAAAR02R262 X
25	4-40 UNC Jack screw	MAP 3XAAAR02R262 X
37	4-40 UNC Jack screw	MAP 4XAAAR02R262 X
09	M3 Jack screw	MAP 1XAAAR01R262 X
15	M3 Jack screw	MAP 2XAAAR01R262 X
25	M3 Jack screw	MAP 3XAAAR01R262 X
37	M3 Jack screw	MAP 4XAAAR01R262 X

SOCKET CONNECTOR / PLUG CONNECTOR WITH HEX BOLT

No. of pos.	Mounting style	Part Number
09	4-40 UNC Hex bolt	MAP 1XAAAH02R262 X
15	4-40 UNC Hex bolt	MAP 2XAAAH02R262 X
25	4-40 UNC Hex bolt	MAP 3XAAAH02R262 X
37	4-40 UNC Hex bolt	MAP 4XAAAH02R262 X
09	M3 Hex bolt	MAP 1XAAAH01R262 X
15	M3 Hex bolt	MAP 2XAAAH01R262 X
25	M3 Hex bolt	MAP 3XAAAH01R262 X
37	M3 Hex bolt	MAP 4XAAAH01R262 X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[MAP3XAAAR01R361X](#) [MAP2XAAAR01R361X](#) [MAP1XAAAR01R361X](#) [MAP3XAAAR01R262X](#)
[MAP2XAAAR01R262X](#) [MAP1XAAAR01R262X](#)