


D-SUB SHIELDED CAP

Metal design – Shielded – Jack screw – Lanyard




RoHS compliant


DESCRIPTION

- Shielded cap protecting against EMI/RFI
- Material:
 - Shell: Steel tin plated
 - Lanyard: Stainless steel
 - Screw: Steel or stainless steel
- Mounting style:
with M3 or 4-40 UNC Jack screw

SOCKET CONNECTOR



PLUG CONNECTOR



50-pos.= Dim. in (..)

No. of pos.	A _{0,76}	B1 _{+0,25}	B2 _{-0,25}	C	D _{-0,3}
09	31.19	16.79	16.46	25.00	6.12
15	39.52	25.12	24.79	33.30	6.12
25	53.42	38.84	38.50	47.04	5.99
37	69.70	55.30	54.96	63.50	5.99
50	67.00	52.81	52.50	61.11	6.12

ORDER DATA

SHIELDED CAP FOR SOCKET CONNECTOR

No. of pos.	Design	Part Number
09	Metal/M3 Jack screw steel / Lanyard	16-000790
15	Metal/M3 Jack screw steel / Lanyard	16-000800
25	Metal/M3 Jack screw steel / Lanyard	16-000810
37	Metal/M3 Jack screw steel / Lanyard	16-000820
50	Metal/M3 Jack screw steel / Lanyard	16-000830
09	Metal/4-40 UNC Jack screw steel / Lanyard	16-000840
15	Metal/4-40 UNC Jack screw steel / Lanyard	16-000850
25	Metal/4-40 UNC Jack screw steel / Lanyard	16-000860
37	Metal/4-40 UNC Jack screw steel / Lanyard	16-000870
50	Metal/4-40 UNC Jack screw steel / Lanyard	16-000890
09	Metal/M3 Jack screw stainless steel / Lanyard	16-000230
15	Metal/M3 Jack screw stainless steel / Lanyard	16-000240
25	Metal/M3 Jack screw stainless steel / Lanyard	16-000250
37	Metal/M3 Jack screw stainless steel / Lanyard	16-000260
50	Metal/M3 Jack screw stainless steel / Lanyard	16-000270
09	Metal/4-40 UNC Jack screw stainless steel / Lanyard	16-000280
15	Metal/4-40 UNC Jack screw stainless steel / Lanyard	16-000290
25	Metal/4-40 UNC Jack screw stainless steel / Lanyard	16-000300
37	Metal/4-40 UNC Jack screw stainless steel / Lanyard	16-000310
50	Metal/4-40 UNC Jack screw stainless steel / Lanyard	16-000320

SHIELDED CAP FOR PLUG CONNECTOR

No. of pos.	Design	Part Number
09	Metal/M3 Jack screw steel / Lanyard	16-000900
15	Metal/M3 Jack screw steel / Lanyard	16-000910
25	Metal/M3 Jack screw steel / Lanyard	16-000920
37	Metal/M3 Jack screw steel / Lanyard	16-000930
50	Metal/M3 Jack screw steel / Lanyard	16-000940
09	Metal/4-40 UNC Jack screw steel / Lanyard	16-000950
15	Metal/4-40 UNC Jack screw steel / Lanyard	16-000960
25	Metal/4-40 UNC Jack screw steel / Lanyard	16-000970
37	Metal/4-40 UNC Jack screw steel / Lanyard	16-000980
50	Metal/4-40 UNC Jack screw steel / Lanyard	16-000990
09	Metal/M3 Jack screw stainless steel / Lanyard	16-000330
15	Metal/M3 Jack screw stainless steel / Lanyard	16-000340
25	Metal/M3 Jack screw stainless steel / Lanyard	16-000350
37	Metal/M3 Jack screw stainless steel / Lanyard	16-000360
50	Metal/M3 Jack screw stainless steel / Lanyard	16-000370
09	Metal/4-40 UNC Jack screw stainless steel / Lanyard	16-000380
15	Metal/4-40 UNC Jack screw stainless steel / Lanyard	16-000390
25	Metal/4-40 UNC Jack screw stainless steel / Lanyard	16-000400
37	Metal/4-40 UNC Jack screw stainless steel / Lanyard	16-000410
50	Metal/4-40 UNC Jack screw stainless steel / Lanyard	16-000420

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[16-000790](#) [16-000870](#) [16-000950](#) [16-000990](#) [16-000980](#) [16-000900](#) [16-000240](#) [16-000420](#) [16-000810](#) [16-000800](#) [16-000960](#) [16-000230](#) [16-000920](#) [16-000850](#) [16-000970](#) [16-000890](#)