




Features


- Intel® Pentium® N4200/ Celeron® N3350 Processor SoC
- Onboard LPDDR4 Memory up to 8GB
- Onboard eMMC Storage up to 128GB
- Gigabit LAN x 2, USB 2.0 x 2, USB 3.0 (Type A) x 3
- 5V DC-in, 4-6A
- 40 pin GPIO x 1
- DP/eDP/HDMI x 1
- MIPI-CSI (4-Lane & 2-Lane) x 1
- Mini-PCle /M.2 2230 x 1
- SATA3 x 1
- 60pin EXHAT



Specifications


System	
Processor	Intel® Pentium® N4200/ Celeron® N3350/ Atom™ E3940/ E3950 Processor SoC
Graphics	Intel® Gen 9 HD, supporting 4K Codec Decode and Encode for HEVC4, H.264, VP8
I/O	HDMI x 1 DP x 1 I2S Audio Port
Camera	CSI 2-Lane + CSI 4-Lane
USB	USB 2.0 x 2 USB3.0 OTG x 1 USB3.0 (Type A) x 3
Expansion	40 pin GPIO x 1 Full-sized Mini-PCle x 1 (PCle & SATA + USB2.0) M.2 2230 x 1 SATA3 x 1 60 pin EXHAT x 1
RTC	Yes
Power	5V DC-in @ 4A-6A
Dimension	3.37" x 3.54" (85.6 mm x 90 mm)
Memory	2GB (single channel) LPDDR4 4GB/8GB (dual channel) LPDDR4
Storage	eMMC 32 GB / 64 GB / 128 GB
Display Interface	eDP
Ethernet	Gb Ethernet (full speed) RJ-45 x 2
OS Support	Microsoft Windows 10 (full), Windows IOT Core, Linux (ublinux, Ubuntu, Yocto), Android Nougat
Operating Temperature	32°F ~ 140°F (0°C ~ 60°C)
Operation Humidity	0% ~ 90% relative humidity, non-condensing
Certification	CE/FCC Class A, RoHS Compliant, REACH

Block Diagram



Dimension

Unit: mm



Ordering Information

Part number	Description
UPS-APLC2F-A20-0232	UP ² (UP Squared) board with Intel® Celeron® Dual Core N3350(F1) up to 2.4GHz, on board 2GB DDR4, 32GB eMMC
UPS-APLC2F-A20-0432	UP ² (UP Squared) board with Intel® Celeron® Dual Core N3350(F1) up to 2.4GHz, on board 4GB DDR4, 32GB eMMC
UPS-APLP4F-A20-0432	UP ² (UP Squared) board with Intel® Pentium® N4200(F1) Quad Core up to 2.5 GHz, on board 4GB DDR4, 32GB eMMC
UPS-APLP4F-A20-0864	UP ² (UP Squared) board with Intel® Pentium® N4200(F1) Quad Core up to 2.5 GHz, on board 8GB DDR4, 64GB eMMC
UPS-APLP4F-A20-08128	UP ² (UP Squared) board with Intel® Pentium® N4200(F1) Quad Core up to 2.5 GHz, on board 8GB DDR4, 128GB eMMC
UPS-APLX5F-A20-0432	UP ² (UP Squared) board with Intel® Atom™ E3940(F1).4G memory 32G eMMC.Rev.1.0
UPS-APLX7F-A20-0464	UP ² (UP Squared) board with Intel® Atom™ E3950(F1).4G memory 64G eMMC.Rev.1.0
UPS-APLX7F-A20-0864	UP ² (UP Squared) board with Intel® Atom™ E3950(F1).8G memory 64G eMMC.Rev.1.0

Packing List

- UPS-APL with Heatsink

Optional Accessories

- **1702020910**
Power cord for EU
- **1702020911**
Power cord for US
- **1255300362**
30W.5VDC/6A power adapter
- **PER-TAICX-A10-001**
AI Core X mPCIe card.with 30 mm heat sink
- **PER-TAICX-A10-002**
AI Core X mPCIe card.with 15 mm heat sink with FAN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AAEON:](#)

[UPS-APLP4F-A20-0864](#) [UPS-APLC2F-A20-0232](#) [UPS-APLC2F-A20-0432](#) [UPS-APLP4F-A20-0432](#) [UPS-APLX5F-A20-0432](#) [UPS-APLX7F-A20-0464](#) [UPS-APLX7F-A20-0864](#) [UPS-APLP4F-A20-08128](#)