

PCRS_LCUX_LCUX_A221T_XX.X_SS

Description

Duplex patch cord, LC uniboot push-pull XD to LC uniboot push-pull XD, UPC, duplex round 2.1mm_XX.X_yellow, SM G.657.A2, A-B / B-A



Features	Features
- High mechanical stability - Colour coded boot for good visibility also in mated condition	

Technical Data

General Data

Description	Values
General Typ	Duplex LC patch cord
Operation temperature	-25 up to 70°C
Polarity	A-B / B-A straight polarity (standard)
UL Rating	UL 94 V-0
RoHS compliant 2001/65/EU	Yes
REACH compliant	Yes

Connector left

Description	Values
Connector typ	LC-XD duplex Uniboot
Polish	UPC
Color Housing	Black
Color Clip	Blue
Color Boot	Black
Design connector acc. To	IEC 61754-20, TIA 604-10-A
Performance class H+S	S
Insertion loss 97% dB / mean dB	0.45 / 0.2
Return Loss	50
Durability	1000
Tensile load	70 N
Tensile load acc. To GR-326-COR	Fulfilled

Connector right

Description	Values
Connector typ	LC-XD duplex Uniboot
Polish	UPC
Color Housing	Black
Color Clip	Blue
Color Boot	Black
Design connector acc. To	IEC 61754-20, TIA 604-10-A
Performance class H+S	S
Insertion loss 97% dB / mean dB	0.45 / 0.2
Return Loss	50
Durability	1000
Tensile load	70 N

PCRS_LCUX_LCUX_A221T_XX.X_SS


Tensile load acc. To GR-326-COR

Fulfilled

Cable

Description	Values
Cable typ	Riser Cable
Fiber count	2
Fiber	2 x 0.6 mm
Fiber type	E9/125-SM G.657.A2
Outer diameter	2.1 mm
Outer jacket material	Jacket material according to UL 94V-0

Technical Drawing



Ordering information

Meter (m)	Item number	Description
1	85016597	PCRS_LCUX_LCUX_A221T_01.0_SS
2	85016599	PCRS_LCUX_LCUX_A221T_02.0_SS
3	85013608	PCRS_LCUX_LCUX_A221T_03.0_SS
3	85016600	PCRS_LCUX_LCUX_A221T_03.0_SS
4	85019951	PCRS_LCUX_LCUX_A221T_04.0_SS
5	85016601	PCRS_LCUX_LCUX_A221T_05.0_SS
5	85013609	PCRS_LCUX_LCUX_A221T_05.0_SS
6	85020819	PCRS_LCUX_LCUX_A221T_06.0_SS
7	85020820	PCRS_LCUX_LCUX_A221T_07.0_SS
10	85016602	PCRS_LCUX_LCUX_A221T_10.0_SS
11	85119362	PCRS_LCUX_LCUX_A221T_11.0_SS
15	85020821	PCRS_LCUX_LCUX_A221T_15.0_SS
20	85020822	PCRS_LCUX_LCUX_A221T_20.0_SS
25	85025976	PCRS_LCUX_LCUX_A221T_25.0_SS
30	85025977	PCRS_LCUX_LCUX_A221T_30.0_SS
1.5	85023034	PCRS_LCUX_LCUX_A221T_01.5_SS
2.5	85025973	PCRS_LCUX_LCUX_A221T_02.5_SS
3.5	85020818	PCRS_LCUX_LCUX_A221T_03.5_SS
4.5	85025974	PCRS_LCUX_LCUX_A221T_04.5_SS
5.5	85025975	PCRS_LCUX_LCUX_A221T_05.5_SS
7.5	85137895	PCRS_LCUX_LCUX_A221T_07.5_SS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[PCRS_LCUX_LCUX_A221T_07.0_](#)