



B

PART NUMBER:

BR-005

REV D

SH 1

REVISIONS

LTR	DESCRIPTION	BY	DATE	APPD
A	NEW RELEASE	DS	5/15/97	JM
B	REVISED PER ECO # 2476	DS	10/26/01	JM
C	REVISED PER ECO # 3189	SG	5/5/04	SRO
C1	REVISED PER EC-00510-UV	JC	11/15/07	SRO
D	REVISED PER EC-00361-UV	JC	7/15/08	SRO

B

B

A

A

NOTES:

1. MATERIAL: 0.062 THK. ALUMINUM ALLOY 5052-H32 PER QQ-A-250/8
2. FINISH: DARK MATTE, BLACK ANODIZED PER MIL-A-8625
3. ALL BENDS ARE TO BE SHARP.
4. REMOVE ALL BURRS AND SHARP EDGES.
5. MARK PART NUMBER AND REVISION. STAMP OR USE A NON-CONDUCTIVE INDELIBLE INK, (FREE OF CARBON) CONTRASTING COLOR, 0.09-0.125 HIGH CHARACTERS LOCATE APPROXIMATELY AS SHOWN. i.e. XX-XXX_revX.

DASH NUMBER	NEXT ASSY	USED ON
APPLICATION		

UNLESS OTHERWISE SPECIFIED DIMENSION ARE IN INCHES TOLERANCES ARE: 2 PL DEC ± .02 FRACT ± 1/64 3 PL DEC ± .010 ANGLES ± 2°			CUSTOMER		
HOLE DIA			DRAWN	DS	DATE
.0135 THRU .125			CHKD	FG	5/15/97
.126 THRU .250			MFG	N/A	6/3/97
.251 THRU .500			MFG ENGR	ISO	6/30/97
.501 THRU .750			PROCESS	N/A	
.751 THRU 1,000			QA	N/A	
1,001 THRU 2,000			CHIEF ENG	JM	5/6/97
			CFN: BR-005_revD.dwg		

ULTRAVOLT, INC. 1800 OCEAN AVE. FRNT, RONKONKOMA, N.Y. 11779 1-631-471-4444		
BRACKET ("25A/30A/35A") WITH & WITHOUT H.S. PLATE (BRACKET KIT OPTION ORDER BR-5 KIT)		
B	PART NUMBER: BR-005	REV D
SCALE NONE	DO NOT SCALE THIS DRAWING	SHEET 1 OF 1

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advanced Energy:](#)

[BR-5 KIT](#)