



PROPRIETARY STATEMENT: ULTRAVOLT INC.
CONFIDENTIAL DRAWING

REVISIONS

LTR	DESCRIPTION	BY	DATE	APPD
A	NEW RELEASE	D.S.	3/4/99	J.M.
A1	REVISED PER EC-00510-UV	JC	11/15/07	SRO

NOTES:

1. MATERIAL: 0.125 THK. ALUMINUM ALLOY 6061-T6
PER QQ-A-250/11
2. FINISH: DARK MATTE, BLACK ANODIZED PER MIL-A-8625,
TYPE II, CL 2.
3. ALL BENDS ARE TO BE SHARP.
4. REMOVE ALL BURRS AND SHARP EDGES.
5. MARK PART NUMBER AND REVISION. STAMP OR USE A
NON-CONDUCTIVE INDELIBLE INK, (FREE OF CARBON)
CONTRASTING COLOR, 0.09-0.125 HIGH CHARACTERS
LOCATE APPROXIMATELY AS SHOWN. i.e. XX-XXX_revX.

DASH NUMBER	NEXT ASSY	USED ON
APPLICATION		

UNLESS OTHERWISE SPECIFIED DIMENSION ARE IN INCHES TOLERANCES ARE: 2 PL DEC ± .02 FRACT ± 1/64 3 PL DEC ± .010 ANGLES ± 2°	
HOLE DIA	TOLERANCES
.0135 THRU .125	+.004 -.004
.126 THRU .250	+.005 -.005
.251 THRU .500	+.006 -.006
.501 THRU .750	+.008 -.008
.751 THRU 1.000	+.010 -.010
1.001 THRU 2.000	+.012 -.012

CUSTOMER		
DRAWN	D.S.	DATE 3/4/99
CHKD	F.G.	3/19/99
MFG	N/A	
MFG ENGR	J.R.O.	3/10/99
PROCESS	N/A	
QA	J. MORRISON	3/16/99
CHIEF ENG	J. MORRISON	3/16/99
CFN: BR-008_revA1.dwg		

ULTRAVOLT, INC. 1800 OCEAN AVE. FRNT, RONKONKOMA, N.Y. 11779 1-631-471-4444		
HIGH POWER "C" SERIES FLUSH MTG BRACKET (BRACKET KIT OPTION ORDER BR-8 KIT)		
B	PART NUMBER: BR-008	REV A1
SCALE NONE	DO NOT SCALE THIS DRAWING	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advanced Energy:](#)

[BR-8 KIT](#)