



SmartRack 1U Rack-Mount Device Rack Extension Bracket, 1.5 in.

MODEL NUMBER: B018-000-1P5



1U rack extensions allow you to fully open your console or console KVM switch when equipment mounted just above it extends past the front rails and prevents the unit from opening.

Description

The B018-000-1P5 1U Rack-Mount Device Rack Extension Bracket allows you to mount a console or console KVM switch into a rack so that it extends 1.5 inches past the front vertical mounting rails. This is of use when the rack equipment mounted just above the console protrudes out the front of the rack and prevents the console from fully opening. The rack-mount extension brackets are constructed from cold-rolled steel with a black powder-coated finish to match your rack. Attach the rack extension brackets to your EIA-standard 19-inch rack, then attach the console or console KVM switch to the brackets. All necessary mounting hardware is included.

Features

Extend Your Rack-Mount Device Past the Front Mounting Rails

- Allows your console or console KVM to fully open when it is being blocked by protruding rack equipment mounted just above it
- Extends 1.5 in. past the front vertical mounting rails
- Cold-rolled steel construction with black powder-coated finish designed for long life
- Compatible with EIA-standard 19 in. racks and rack cabinets
- All necessary mounting hardware is included

Specifications

OVERVIEW	
UPC Code	037332206244
Accessory Type	Mounting Bracket; Rackmount Kit
Accessory Class	Rack Accessories
VIDEO	

Highlights

- Extends 1.5 in. past the front vertical mounting rails
- Made from cold-rolled steel with black powder-coated finish
- Compatible with EIA-standard 19 in. racks and rack cabinets
- All necessary mounting hardware is included

Package Includes

- (2) Rack extensions
- (8) M6 screws
- (8) M6 cage nuts
- (8) M6 cup washers
- Installation guide



Powering Business Worldwide

TRIPP LITE
SERIES

3D Video Supported	No
INPUT	
Bus Powered	No
POWER	
Power Over Cable (PoC) Support	No
PHYSICAL	
Color	Black
Rackmountable	No
Shipping Dimensions (hwd / in.)	1.77 x 3.34 x 1.77
Shipping Dimensions (hwd / cm)	4.50 x 8.48 x 4.50
Shipping Weight (lbs.)	0.37
Shipping Weight (kg)	0.17
Unit Dimensions (hwd / in.)	1.720 x 1.500 x 0.640
Unit Packaging Type	Box
COMMUNICATIONS	
EDID Compatible	No
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	No
FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	No
IP68 Rated	No
IP20 Rated	No
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B018-000-1P5](#)