

RG6/U Quad-Shield CMR-Rated Coaxial Cable, White, 1000 ft. (304.8 m)

MODEL NUMBER: A224-01K-WH



Highlights

- Lower attenuation than RG59 cable for longer distances
- 18 AWG copper-clad steel center conductor
- Quad foil and braid shielding for error-free transmission
- Flame-retardant CMR-rated PVC jacket
- Meets UL1655, UL13, UL444 and RoHS standards

Package Includes

- A224-01K-WH RG6/U Quad-Shield CMR-Rated Coaxial Cable, White, 1000-ft. (304.8 m)

Premium coaxial cabling designed for high-frequency indoor/outdoor applications, such as television antennas, digital cable and satellite transmissions, and video surveillance systems.

Features

Coaxial Cabling for High-Frequency Indoor/Outdoor Applications Ideal for television antennas, digital cable and satellite transmissions, and video surveillance systems **White** 75-ohm cable tested to 3 GHz **Lower attenuation than RG59 cable for longer distances** **Premium Construction for Superior Performance** 18 AWG copper-clad steel center conductor Quad foil and braid shielding for error-free transmission Flame-retardant CMR-rated PVC jacket Meets UL1655, UL13, UL444 and RoHS standards

Specifications

OVERVIEW	
UPC Code	037332196415
Technology	Coax; RG59/RG6
CONNECTIONS	
Side A - Connector 1	BARE WIRE
Side B - Connector 1	BARE WIRE
Crossover Wiring	No
Connector Type	Bare Wire
Latching or Gripping Connector	No
PHYSICAL	
Cable Jacket Color	White
Cable Jacket Material	PVC



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Jacket Rating	CMR
Cable Length (ft.)	1000
Cable Length (m)	304.88
Shipping Dimensions (hwd / in.)	9.45 x 20.87 x 20.87
Shipping Dimensions (hwd / cm)	24.00 x 53.01 x 53.01
Shipping Weight (lbs.)	35.00
Shipping Weight (kg)	15.88
FEATURES & SPECIFICATIONS	
Antibacterial	No
IP68 Rated	No
Snagless Connector	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[A224-01K-WH](#)