

2-Port DisplayPort to VGA Hub, DP1.2, TAA

MODEL NUMBER: B157-002-VGA



Converts and splits a DisplayPort video signal for display on two VGA monitors, projectors or televisions at the same time. Ideal for offices, conference rooms, retail settings, trade shows and classrooms.

Description

The B157-002-VGA 2-Port DisplayPort to VGA Splitter converts and splits a DisplayPort video signal for display on two VGA-enabled monitors, projectors or televisions at the same time. Ideal for offices, conference rooms, retail settings, trade shows and classrooms, this compact splitter features a built-in DisplayPort cable that connects to the source. It lets you use your existing VGA displays instead of buying new DisplayPort monitors or docking stations.

The B157-002-VGA supports video resolutions up to 1080p @ 60 Hz (1920 x 1080), as well as HDCP, EDID and DDC. Orange LEDs next to each output port indicate whether the splitter is powered on and transmitting a signal to the connected displays. The splitter works with all operating systems and is small enough to carry in your backpack or computer bag. Plug-and-play convenience means no software or drivers are needed. An included USB Micro-B cable connects between the source and the splitter to provide power, so no external power supply is required.

Features

Converts and Splits DisplayPort Signal to 2 VGA Displays Simultaneously Ideal for offices, conference rooms, trade shows and classrooms
Built-in DisplayPort cable connects to source
Included USB Micro-B cable supplies power to splitter
Save money on new DisplayPort displays or docking stations

Top-Shelf Performance Supports video resolutions up to 1080p @ 60 Hz (1920 x 1080)
 Complies with HDCP, EDID and DDC
 LEDs indicate whether splitter is powered on and transmitting signal to connected displays

Easy to Use Almost Anywhere Works with all operating systems
 Plug and play—no software, drivers or external power supply required
 Compact unit fits easily in backpack or computer bag

Highlights

- Supports video resolutions up to 1080p @ 60 Hz (1920 x 1080)
- Included USB Micro-B cable supplies power to unit
- Works with all operating systems
- Compact enough for easy carrying in backpack or laptop bag
- Plug and play—no software or drivers required

Package Includes

- B157-002-VGA 2-Port DisplayPort to VGA Splitter
- USB Micro-B cable, 3 ft.
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332191496
Product Type	Splitter
Technology	VGA/SVGA; DisplayPort



Powering Business Worldwide

TRIPP LITE
SERIES

Host Connector	DISPLAYPORT (FEMALE)
VIDEO	
Max Supported Video Resolution	1920 x 1080 (1080p) @ 60Hz
Max Supported Color Depth	24-bit True Color
3D Video Supported	Yes
AUDIO	
Audio Specification	2.0-channel surround sound audio
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	DISPLAYPORT (MALE)
Side A - Connector 2	MICRO-USB B (FEMALE)
Side B - Connector 1	(2) HD15 (FEMALE)
Connector Plating	Nickel
Input x Output	1 x 2
Daisy-chainable / Cascadable	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	(x2) Orange (Monitor Signal)
PHYSICAL	
Color	Black
Material of Construction	Metal
Wire Gauge (AWG)	28
Cable Length (ft.)	0
Cable Length (m)	0.00
Shipping Dimensions (hwd / in.)	1.70 x 7.90 x 5.60
Shipping Dimensions (hwd / cm)	4.32 x 20.07 x 14.22
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	2.55 x 6.15 x 7.6
Unit Dimensions (hwd / mm)	25.5 x 61.5 x 76
Unit Weight (lbs.)	0.154
Unit Weight (kg)	0.07



Powering Business Worldwide

TRIPP LITE
SERIES

COMMUNICATIONS	
EDID Compatible	Yes
FEATURES & SPECIFICATIONS	
MST Support	No
Displayport Specification	1.2
HDCP Specification	1.3
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B157-002-VGA](#)