

## Cover Options - Single Row

### Terminal Block Covers

Available for A1, A2, A3, A4 & B4, LP2, & LP3 (mount ends only)

Three styles of UL 94V0 thermoplastic covers are offered in black. Covers are ordered separately and supplied with two clips each, unless ordered without clips. Optional markings may be specified (white on black).


Notes: Covers **cannot** be used with:

- mounting plate options MP & MT.
- certain quick connect terminals.
- 6 base/end styles on A2

Bulk Cover Clips: A1 Family = **CC1-J**; A2, A3, LP2 & LP3 Family = **CC2-J**; A4 & B4 Family = **CC4-J**.


#### Standard Cover Markings

Top Forward - TF



Bottom Forward - BF  
Skirted Access Side


Top Reverse - TR




Bottom Reverse - BR  
Skirted Access Side



**Cover Options BB**  
Skirted access on both sides.



**Cover Options BO**  
Skirted access on one side only.



**Cover Options BC**  
Open access on both sides.

#### Cover



**BB** - skirted access, both sides, black

**BO** - skirted access, one side, black

**BC** - open access, both sides, black\*

\* Not available in 4000

#### Poles



**1** - A1

**2** - A2, LP2

**3** - A3, LP3

**4** - A4, B4

#### Markings (if desired)




**BF** - bottom forward

**TF** - top forward

**BR** - bottom reverse

**TR** - top reverse

#### Options



**00** - without clips

## Snap-On Covers for A38/B38/A0 & CB2/CB3

Can be used on both mount ends and barrier bases

### A38/B38/A0



### CB2/CB3



**T A 8** - [ ] [ ] **A38**

**T B 8** - [ ] [ ] **B38**

**T A 0** - [ ] [ ] **A0**

#### Poles

**T O 2** - [ ] [ ] **CB2**

**T O 3** - [ ] [ ] **CB3**

Note: these are labeled as the letter "O" not a "zero"

## Tools & resources

- [Webpage](#)
- [Terminal block selector tool](#)
- [Terminal block cross reference](#)
- [Contact us](#)

**Eaton**  
**Electronics Division**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
[Eaton.com/electronics](http://Eaton.com/electronics)

© 2019 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 10682 — BU-MC19146  
November 2019

Eaton is a registered trademark.

All other trademarks are property  
of their respective owners.

Follow us on social media to get the  
latest product and support information.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Eaton:

[TB3-D](#) [BB3-02BF](#) [TB8-02](#) [BB1-03](#) [TA8-08](#) [BB2-08-00](#) [TA8-03](#) [BB3-04BF](#) [BB3-04TF](#) [BB3-04](#) [BB3-10](#) [BB3-11TF](#)  
[BB1-17](#) [BB2-02](#) [BB2-03](#) [BB2-03BF](#) [BB2-04](#) [BB2-05](#) [TA0-14](#) [TA0-15](#) [BB4-06TF](#) [BB1-06TF-J](#) [BB4-09](#) [BB4-10](#)  
[BB4-12](#) [BO3-04TF](#) [BB4-02TF](#) [BB4-03](#) [BB4-04](#) [BB4-05](#) [BB4-06](#) [BC3-11](#) [BC3-20](#) [BO2-03-00](#) [BO2-04-00](#) [BO3-](#)  
[03BR](#) [BO3-04BF](#) [TA0-10](#) [TA0-11](#) [TA0-12](#) [TA0-13](#) [BC3-07](#) [BC3-08](#) [TA0-04](#) [TA0-05](#) [TA0-06](#) [TA0-07](#) [TA0-08](#)  
[TA0-09](#) [TA0-29](#) [TA0-30](#) [TB8-07](#) [TB8-09](#) [TA0-02](#) [TA0-03](#) [TA0-23](#) [TA0-24](#) [TA0-25](#) [TA0-26](#) [TA0-27](#) [TA0-28](#) [TB8-](#)  
[10](#) [TB8-11](#) [TB8-14](#) [TB8-15](#) [TB8-16](#) [TO3-02](#) [TA0-17](#) [TA0-18](#) [TA0-19](#) [TA0-20](#) [TA0-21](#) [TA0-22](#) [BC3-06-00](#) [BO3-](#)  
[09](#) [BO3-09TR](#) [BO3-19](#) [BO4-08BR](#) [TA0-16](#) [BC2-08TR](#) [BC2-09-00](#) [BC3-02](#) [BC3-04BF](#) [BC3-05-00](#) [BC3-05TF](#)  
[BC2-03-00/J](#) [BCC-10](#) [BC2-03TF](#) [BCF-20](#) [BCF-3](#) [BCC-15](#) [BCC-1-8/10](#) [BCC-1-1/8](#) [BCF-5](#) [BC2-10BF](#) [BCF-30](#)  
[BCF-15](#) [BCF-10](#) [BCC-5](#) [TA8-02](#)