

Telpower® 70-600A: 170Vdc fuses

TPL

Specifications

Description: DC power distribution fuses for use with Telpower 15100, 15200, TP158HC and TPHCS disconnect systems. For replacement of Cooper Bussmann UBO fuses a TPL-TA adapter kit is necessary.

Dimensions: See Dimensions illustrations.

Construction: Silver-plated terminals.

Ratings:

Volts: — 170Vdc
Amps: — 70-800A
IR: — 100,000A

Agency Information: CE, UL Recognized Guide JFHR2, File E56412 Bellcore.

Features and Benefits

- Current-limiting capability designed for dc power distribution systems
- Recognized branch circuit protection
- Complete system coordination capability
- Energy savings with low watts loss, low operating temperatures, and minimum I²t levels

Typical Applications

- Telecommunications power circuit protection

Catalog Numbers


Catalog Numbers	Amp Rating
TPL-BA	70
TPL-BB	80
TPL-BC	90
TPL-BD	100
TPL-BE	125
TPL-BF	150
TPL-BG	175
TPL-BH	200
TPL-BK	225
TPL-BL	250
TPL-CN	300
TPL-CO	350
TPL-CR	400
TPL-CU	450
TPL-CV	500
TPL-CZ	600
TPL-CZH	800

Accessories


- Spare fuse holders: TPSFH-LB (for TPL-B fuses)
TPSFH-LC (for TPL-C fuses)



Dimensions - in (mm)



TPL-BA, TPL-BD, TPL-BF, TPL-BH, TPL-BK, AND TPL-BL



TPL-CN, TPL-CR, TPL-CV, AND TPL-CZ



Did You Know?

Web Services

www.cooperbussmann.com

The Cooper Bussmann web site makes available free information and other resources that include:

- Product Data Sheets for complete technical information on Bussmann products
- Online catalogs for the latest United States and European products
- Fuse Cross Reference to find the correct Bussmann replacement for a competitive fuse
- Arc-Flash Calculator to determine the incident energy level and flash protection boundary along with the recommends the level of Personal Protective Equipment (PPE)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[TPL-BA](#) [TPL-BB](#) [TPL-BC](#) [TPL-BD](#) [TPL-BF](#) [TPL-BG](#) [TPL-BK](#) [TPL-BH](#) [TPL-BL](#) [TPL-BE](#) [TPL-CN](#) [TPL-CO](#) [TPL-CV](#) [TPL-CR](#) [TPL-CU](#) [TPL-CZ](#) [TPL-CZH](#)