

AGW

1/4" x 7/8" Fast-acting glass tube fuses



Ordering information

- Specify product code
- Insert packaging code prefix before part number, E.g., BK/AGW-1


Product features

- Fast-acting
- 1/4" x 7/8" (6.3 x 22.2mm) physical size
- Glass tube, nickel-plated brass endcap construction
- Mounts in in-line holders HHB (data sheet # 2103), HHK, HRK (data sheet # 2111) or PCB fuse clips for 1/4" fuses (1A1119, 1A1120, 1A1907, 1A3398, 1A4533 and 1A4534 - data sheet # 2131)


Specifications				
Part Number (Amps)	Voltage Rating Vac	Interrupting Rating (amps) at Rated Voltage AC	Typical DC Cold Resistance (Ω)*	
			Lower	Upper
AGW-1	32	1000	0.100	0.135
AGW-1½	32	1000	0.060	0.080
AGW-2	32	1000	0.042	0.056
AGW-2½	32	1000	0.029	0.040
AGW-3	32	1000	0.027	0.036
AGW-4	32	1000	0.018	0.024
AGW-5	32	1000	0.013	0.018
AGW-6	32	1000	0.010	0.014
AGW-7½	32	1000	0.009	0.012
AGW-10	32	1000	0.006	0.008
AGW-15	32	1000	0.003	0.005
AGW-20	32	1000	0.002	0.003
AGW-25	32	1000	0.002	0.003
AGW-30	32	1000	0.001	0.002

* DC Cold Resistance (Measured at <10% of rated current)

Dimensions - in



Time-Current Curves



Packaging Code	
Packaging Code Prefix	Description
BK	100 fuses packed into a cardboard carton

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
www.eaton.com/electronics

© 2017 Eaton
All Rights Reserved
Printed in USA
Publication No. 2040 BU-SB13900
June 2017

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[AGW-1-1-2](#) [AGW-2-1-2](#) [AGW-7-1-2](#) [BK-AGW-1](#) [BK-AGW-10](#) [BK-AGW-15](#) [BK-AGW-2](#) [BK-AGW-20](#) [BK-AGW-2-1-](#)
[2](#) [BK-AGW-3](#) [BK-AGW-30](#) [BK-AGW-4](#) [BK-AGW-5](#) [BK-AGW-6](#) [BK-AGW-7-1-2](#) [AGW-2](#)