



Eaton TVS diode ESD suppressors: selection and sizes

Package size	Family	Reverse working voltage	ESD withstand range	Peak pulse current (8/20 µs)	Capacitance range
DFN0603	STN061050B300	5.0 V	30 kV	Up to 7 A	4 pF
	STN06XXXB101	3.3 V to 5.0 V	30 kV	Up to 7 A	10 pF
	STN06XXXB15	3.3 V to 5.0 V	15 kV	Up to 4 A	0.15 pF
	STN061050BL40	5.0 V	18 kV to 20 kV	Up to 5 A	0.4 pF
DFN1006	STN10XXXXLXX	5.0 V	15 kV	Up to 5 A	0.8 pF to 0.9 pF
	STN101XXBXXX	3.3 V to 12 V	30 kV	Up to 8 A	10 pF to 11 pF
	STN101050B301	5.0 V	30 kV	Up to 20 A	30 pF
	STN101050BL30	5.0 V	20 kV	Up to 4.5 A	0.3 pF
	STN101050BL25	5.0 V	25 kV	Up to 5 A	.25 pF
DFN1610	STN161XXXUXXX	5.0 V to 15 V	30 kV	Up to 110 A	330 pF to 850 pF
DFN2x2	STN202XXXUXXX	7.5 V to 24 V	30 kV	Up to 240 A	750 pF to 1700 pF
DFN2010	STN204033BL60	3.3 V	30 kV	Up to 20 A	1.0 pF
DFN2510	STN254033UL33 & STN254033UL50	3.3 V	15 kV	Up to 3 A	0.2 pF to 0.5 pF
	STN254050UL50 & STN254050UL50H	5.0 V	15 kV to 20 kV	Up to 5 A	0.25 pF to 0.5 pF
	STN265033U380	3.3 V	30 kV	Up to 25 A	2 pF to 3.8 pF
SOT23-6L	STS234XXXUXXX	3.3 V to 5.0 V	20 kV to 30 kV	Up to 24 A	0.3 pF to 3 pF
SOD-523	STS521XXXUXXX	3.3 V to 36 V	15 kV to 30 kV	Up to 10 A	16 pF to 110 pF
	STS521XXXBXXX	3.3 V to 5.0 V	8 kV to 30 kV	Up to 20 A	0.9 pF to 95 pF
SOD-323	STS32XXXXUXXX	5.0 V to 15 V	30 kV	Up to 110 A	330 pF to 850 pF
	STS321XXBXX0	3.3 V to 24 V	30 kV	Up to 20 A	1 pF
	STS321XXBXX1	3.3 V to 36 V	30 kV	Up to 30 A	14 pF to 40 pF
	STS321XXXUXXX	3.3 V to 36 V	8 kV to 30 kV	Up to 25 A	35 pF to 200 pF
	STS321045B502	4.5 V	30 kV	Up to 140 A	450 pF
SOT23	STS232033U202	3.3 V	15 kV	Up to 25 A	200 pF
	STS232050UL40	5.0 V	20 kV	Up to 4 A	0.2 pF to 0.4 pF
	STS232120U901	12 V	30 kV	Up to 20 A	45 pF to 90 pF
	STS232712B451	7.0 V to 12 V	15 kV	Up to 12 A	45 pF to 75 pF
	STS232XXXUXXX	3.3 V to 36 V	15 kV	Up to 18 A	26 pF to 150 pF
SOT-143	STS232XXXBXXX	3.3 V to 36 V	15 kV to 30 kV	Up to 20 A	15 pF to 100 pF
	STS142XXXUXXX	5.0 V to 70 V	20 kV to 30 kV	Up to 24 A	0.4 pF to 0.8 pF
SOP-8	STSP84XXXXXX	2.8 V to 15 V	15 kV to 30 kV	Up to 12 A	0.65 pF to 60 pF

Eaton
Electronics Division
 1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
Eaton.com/electronics

© 2021 Eaton
 All Rights Reserved
 Printed in USA
 Publication No. 11009 BU-MC19136
 June 2021

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[STS521050B331](#) [STS521050B750](#) [STS521050BL90](#) [STS521033B950](#) [STS521050B250](#)