

## Wireless Access Point Enclosure with Hasp - NEMA 4, Surface-Mount, PC Construction, 15 x 11 in.

MODEL NUMBER: **EN1511N4LATCH**



Protects your indoor or outdoor Wi-Fi access point against water, dust, rain, sleet, snow and ice, as well as theft, damage or tampering.

### Features

#### Wall-Mount Enclosure Secures and Organizes Your Router/Modem or Wireless Access

**Point** Protect your indoor or outdoor router/modem or Wi-Fi access point by installing it inside this SmartRack® NEMA 4 Wireless Access Point Enclosure made from impact-resistant UL 94 V-1 Classified PC plastic. It's ideal for offices, dorms, hotels, classrooms, retail locations and other indoor/outdoor areas where you need to keep Wi-Fi equipment secure, organized and out of the way.

**Carries a NEMA 4 Rating for Protection Against Harsh Elements** The NEMA 4-rated enclosure supports indoor or outdoor use. It protects its contents against the ingress of water (including rain, sleet, snow, splashing water and hose-directed water), solid foreign objects (including falling dirt and windblown dust) and even ice forming on the outside of the enclosure.

**Accommodates a Wide Range of Equipment, Including Cisco WAPs, up to 627.5 in.<sup>3</sup>** Though the EN1511N4LATCH is designed specifically to protect Cisco Wi-Fi access points, it will also house most other equipment up to 627.5 cubic inches (10,283 cubic centimeters). While rugged enough to keep your equipment safe inside, it's also transparent to wireless signals, ensuring strong Wi-Fi coverage.

**Latches Securely to Help Prevent Theft, Damage or Tampering** The hinged polycarbonate plastic cover latches tightly to the enclosure to protect the contents. Attach a padlock or tamper seal (both sold separately) to the hasp on the latch for an extra level of security.

**Supports Wall- or Ceiling-Mounting to Best Fit Your Application** The EN1511N4LATCH comes fully assembled and ready for horizontal or vertical mounting on a wall or ceiling with user-provided hardware. It is designed for Cisco WAPs, but the included universal T-bar bracket will accommodate a wide variety of equipment from other brands.

### Highlights

- Designed for Cisco WAPs, but accommodates equipment from most vendors
- NEMA 4 rating ensures protection against water, dust, rain, sleet, snow and ice
- Rugged polycarbonate cover with hasp accepts optional padlock for extra security
- Transparent to wireless signals, ensuring an optimum Wi-Fi signal in all directions
- Comes fully assembled and ready for wall- or ceiling-mounting using included hardware

### Applications

- Protect a router/modem or wireless access point inside a classroom, office, hotel, store, dorm or other indoor space from damage, theft or tampering
- Protect outdoor equipment against water, dust, rain, sleet, snow and ice

### Package Includes

- NEMA 4 wireless access point enclosure, 15 x 11 in.
- (2) M4 screws
- (2) M6 screws, 1 in.
- (4) M6 trusshead screws, 0.25 in.
- Cable tie
- (2) Nylon spacers
- T-bar bracket
- (4) Mounting feet
- Installation guide

## Specifications

### OVERVIEW



Powering Business Worldwide



UPC Code	037332217844
Rack Type	Enclosure
<b>PHYSICAL</b>	
Color	White
Material of Construction	UL 94 V-1 Classified PC Plastic
Rack Height	0U
Maximum Device Depth (cm)	9.65
Maximum Device Depth (in.)	3.8
Maximum Device Depth (mm)	97
Shipping Dimensions (hwd / in.)	6.12 x 13.50 x 16.75
Shipping Dimensions (hwd / cm)	15.56 x 34.29 x 42.54
Shipping Weight (kg)	3.63
Unit Dimensions (cm)	38.6 x 28.2 x 10.16
Unit Dimensions (hwd / in.)	15.000 x 11.000 x 4.000
Unit Dimensions (hwd / cm)	38.6 x 28.2 x 10.16
Unit Dimensions (in.)	15.1 x 11.2
Unit Weight (lbs.)	6.3
Unit Weight (kg)	2.86
Interior Dimensions (hwd / in.)	14.65 x 10.71 x 3.34
Interior Dimensions (hwd / mm)	372.2 x 272.2 x 84.9
<b>FEATURES &amp; SPECIFICATIONS</b>	
Built-in Cable Management	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	NEMA 4; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[EN1511N4LATCH](#)