

## USB (2-in-1) Cable Kit for NetDirector KVM Switch B020-Series and KVM B022-Series, 19 ft. (5.79 m)

MODEL NUMBER: **P776-019**



### Description

This USB (2-in-1) KVM cable kit is designed to connect a USB computer to B020- and B022-Series KVM Switches. The KVM Switch side of the cable kit consists of a HD15 Male cable. The computer side of the cable kit consists of a HD15 Male cable and a USB-A Male cable. This low-profile cable is incredibly flexible, making cable management a breeze. All cables are manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection.

### Features

- Connects a USB computer to B020- and B022-Series KVM Switches
- KVM Switch side of the cable kit consists of a HD15 Male cable
- Computer side of the cable kit consists of a HD15 Male cable and a USB A Male cable
- Provides superior performance and cable management
- Molded ends with easy-grip textured overmold
- Low profile cable is super flexible and easy to control
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection

## Specifications

| OVERVIEW        |                        |
|-----------------|------------------------|
| UPC Code        | 037332147080           |
| Accessory Type  | Cable Kit              |
| Technology      | VGA/SVGA               |
| Accessory Class | KVM Switch Accessories |
| PHYSICAL        |                        |

### Highlights

- Connects a USB Computer to B020- and B022-Series KVM Switches
- Makes management and organization of cables much easier
- KVM Switch side of the cable kit consists of a HD15 Male cable
- Computer side of the cable kit consists of a HD15 Male cable and a USB A Male cable
- Molded, color-coded connectors

### System Requirements

A B020- or B022-Series KVM switch

### Package Includes

- P776-019 19-ft. (5.79 m) KVM Switch USB (2-in-1) Cable Kit

|                                     |                           |
|-------------------------------------|---------------------------|
| Cable Length (ft.)                  | 19                        |
| Cable Length (m)                    | 5.79                      |
| Shipping Dimensions (hwd / in.)     | 0.50 x 6.00 x 8.00        |
| Shipping Dimensions (hwd / cm)      | 1.27 x 15.24 x 20.32      |
| Shipping Weight (lbs.)              | 0.90                      |
| Shipping Weight (kg)                | 0.41                      |
| STANDARDS & COMPLIANCE              |                           |
| Product Compliance                  | RoHS                      |
| WARRANTY & SUPPORT                  |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P776-019](#)