

Power Cord Adapter, C8 to C13 - 10A, 125V, Black

MODEL NUMBER: P003-000



Highlights

- Recommended for powering laptops, video game systems and other C7 peripherals
- Converts a C7 connector into a C13 connector to match available C14 inlet

Applications

- Connect a laptop, video game console or other device with a C7 plug to a C14 inlet

Package Includes

- P003-000 IEC C8 to IEC C13 Power Cord Adapter, Black

C8 to C13 adapter allows you to connect your laptop or other device with a C7 plug to a UPS with a C14 power inlet.

Features

IEC C8 to IEC C13 Adapter Connects Laptops, Video Game Consoles and Other Equipment This UL-listed power cord adapter is designed for home/office setups. It converts a C7 plug into a C13 connector and is ideal for a device's built-in power cord that doesn't match the available outlet. You can use this adapter to connect a laptop, video game system, radio, printer or other device with a C7 plug to a surge protector or UPS system with C14 power inlets.

Specifications

OVERVIEW	
UPC Code	037332217967
Device Compatibility	Laptop; Video Game System; Radio; Printer; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	IEC-320-C8
Side B - Connector 1	IEC-320-C13
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Plug Color	Black
Cable Length (ft.)	0
Cable Length (m)	0.00
Shipping Dimensions (hwd / in.)	5.00 x 3.98 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.11 x 1.27
Shipping Weight (lbs.)	0.07
Shipping Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Operating Humidity Range	30% to 80% RH
Storage Humidity Range	30% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P003-000](#)