

# Portable Power Expansion Hub for Apple USB-C Power Adapter - 4 Ports (3 USB-A, 1 USB-C 45W)

MODEL NUMBER: U280-A04-A3C1



Compact hub expands your Apple USB-C PD Charger from one to 4 charging ports, allowing you to charge 4 mobile devices at the same time.

## Features

**All-in-One Charger Adapter Allows You to Charge up to 4 Devices at the Same Time** This portable charger expansion hub attaches to the 61W or 87W AC wall charger that came with your Apple MacBook Pro to expand the number of charging ports from one to four. A white LED indicates sufficient charging power is available for your devices.

**Connect Your Devices to a USB-C Port and 3 USB-A Ports for Pure Charging** The USB-C PD 3.0 port produces a maximum power output up to 20V 2.25A (45W). A USB-A Quick Charge 3.0 port offers charging speeds up to four times faster than conventional USB wall chargers for compatible devices. The remaining two USB-A BC 1.2 ports supply up to 5V 2.4A for charging. All four ports can be utilized simultaneously to keep your MacBook, Chromebook, smartphones and tablets ready to use.

**Dedicated to Keeping Your Expensive Gadgets Safe** The U280-A04-A3C1 protects your connected devices against overcharging, overheating, overvoltage and short circuits. The unit's non-slip grip padding provides a secure connection to the power adapter. It is colored white and molded to integrate perfectly with the Apple charger and help you reduce unsightly cable clutter.

## Highlights

- Expands an Apple MacBook Pro 61W/87W PD charger to 3 USB-A and 1 USB-C ports
- USB-C PD 3.0 port features maximum power output up to 20V 2.25A (45W)
- USB-A QC 3.0 port charges up to 4 times faster than conventional USB wall chargers
- Dual USB-A BC 1.2 ports supply up to 5V 2.4A power for keeping devices at capacity
- Protects connected devices against overcharging, overheating and short circuits

## Applications

- Charge up to 4 devices at the same time, including iPhones, iPads, MacBooks, Chromebooks, Android smartphones and Windows tablets
- Carry in your laptop bag or backpack, rather than multiple chargers, for charging all your devices at once when away from home or office

## Package Includes

- U280-A04-A3C1 Portable Power Expansion Hub, 4 Ports
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	037332247469
Product Type	Wall Charger
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle; Laptop; Chromebook
INPUT	
Nominal Input Voltage(s) Supported	12V DC



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

Input Plug Type	USB-C (MALE)
<b>OUTPUT</b>	
Overload Protection	Yes
<b>POWER</b>	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.0
<b>CONNECTIONS</b>	
Number of Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (FEMALE)
Side B - Connector 2	(3) USB A (FEMALE)
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	White (Connection to Power)
<b>CHARGING</b>	
Number of Charging Ports	4
Total Charging Amps	5.15A
Total Charging Watts	45
Charging Method	USB
Charging Port Type	(3) USB A (FEMALE); USB C (FEMALE)
Charging Ports Details	USB-C: 20V 2.25A (45W) QC3.0: 12V 1.5A (18W)USB-A: 5V/2.4A (12W)
Charging Ports / Amps	(1) 1.5A; (1) 2.25A; (2) 2.4A
<b>PHYSICAL</b>	
Color	White
Material of Construction	Plastic
Unit Dimensions (hwd / in.)	3.150 x 4.920 x 3.350
Unit Packaging Type	Box
Unit Weight (lbs.)	0.29
Unit Weight (kg)	0.13
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	41° to 95°F (5° to 35°C)
Storage Temperature Range	-4° to 122°F (-20° to 50°C)

Relative Humidity	20% to 80% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Quick Charge Compliant	3.0
Driver Required	No
STANDARDS & COMPLIANCE	
Product Certifications	EN 55024; EN 55032
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U280-A04-A3C1](#)