

USB-C to USB-B Cable (M/M) - USB 3.2 Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 20 in. (51 cm)

MODEL NUMBER: U422-20N-G2



Connects a printer, hub or other USB-B device to your laptop, MacBook, Chromebook or Ultrabook's USB-C or Thunderbolt 3 port.

Features

Connects a USB-B Printer, Scanner or External Hard Drive to Your Laptop's USB-C Port This USB-C to USB Type-B cable allows you to connect a printer, scanner, hard drive, docking station, optical drive or other existing USB-B peripheral to any device with a USB-C or Thunderbolt 3 port, including MacBooks, Ultrabooks and Chromebooks. Its 20-inch (51-centimeter) length makes it easy to carry in your briefcase or laptop bag for quick downloads and file transfers on the go.

Transfers Data and Charges Devices at Lightning-Fast USB 3.2 Gen 2 Speeds The USB Type-C to USB Type-B cable supports USB 3.2 Gen 2 data transfer rates up to 10 Gbps, which is double the speed of USB 3.2 Gen 1.

Reversible USB-C Connector Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Highlights

- USB-C to USB Type-B cable compatible with USB-B, USB-C and Thunderbolt 3 devices
- Supports USB 3.2 Gen 2 speeds up to 10 Gbps to ensure lightning-fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect a printer or scanner to the USB-C or Thunderbolt 3 port on your computer or laptop
- Charge and sync a USB-C or Thunderbolt 3 mobile device from a USB-B wall charger up to 20 in. away
- Connect your laptop to a docking station or hub with a USB-B port

System Requirements

- Devices with USB-C or Thunderbolt 3 ports
- Devices with USB-B ports
- USB 3.2 Gen 2 compatibility required in both connected devices to achieve USB 3.2 Gen 2 speeds

Package Includes

- U422-20N-G2 USB-C 3.2 Gen 2 to USB Type-B Cable (M/M), 20 in. (51 cm)

Specifications

OVERVIEW	
UPC Code	037332243416
Technology	Thunderbolt; USB 3.x
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB B (MALE)



Powering Business Worldwide

TRIPP LITE
SERIES

Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Cable Length (ft.)	1.7
Cable Length (m)	0.52
Cable Length (in.)	20
Cable Length (cm)	50.8
Shipping Weight (lbs.)	0.00
Shipping Weight (kg)	0.00
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10 to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.2 Gen 2 (Up to 10 Gbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U422-20N-G2](#)