

Portable Charger - 2x USB-A, USB-C with PD Charging, 10,050mAh Power Bank, Lithium-Ion, USB-IF, Black

MODEL NUMBER: UPB-10K0-2U1C



Compact 10,050mAh power bank charges up to 3 smartphones, tablets, e-readers and other mobile devices without using an AC power outlet.

Features

10,050mAh Lithium-Ion Battery Charges Your Mobile Devices without an AC Power OutletNo more frantic searching for an outlet when your mobile device's battery power is getting low. Small and lightweight, this high-capacity power bank dishes out 10,050mAh of battery capacity for charging up to three mobile devices at the same time, including smartphones, tablets, e-readers and handheld gaming devices. Lithium-ion lasts longer than lead-acid batteries, charges faster and saves you money in the end. The UPB-10K0-2U1C is compatible with Android, Apple and Windows devices.

3 USB Ports Allow You to Keep Your Phone and Other Essential Devices Ready for UseDual USB-A ports provide 5V 2.4A (12W) of total power per port and feature 1.5A of fast-charging power for Apple devices. The USB-C port supports PD charging up to 5V 3A (15W), 9V 2A (18W) and 12V 1.5A (18W). All three ports provide a maximum of 30W of charging power simultaneously.

Protects Your Expensive Devices During ChargingComprehensive safety features ensure worry-free charging of mobile devices. The power bank provides short circuit, overvoltage, overcurrent, overcharge and overdischarge protection.

Easy and Quick to Recharge for the Next Time You Leave HomeA lithium-ion battery with 10,050mAh of capacity provides charging at maximum power draw for hours, making your devices ready when you need them. Status LEDs let you know how much battery capacity is left. When it's time to charge the internal battery, use the included USB-C cable to connect the power bank's USB-C port to a USB-C port on a computer or wall charger.

USB-IF Certification Ensures Rigorous Testing and Top-of-the-Line PerformanceThis power bank meets the high standards of USB-IF (USB Implementers Forum, Inc.), a non-profit organization consisting of companies that developed the USB specification. Receiving USB-IF certification means the UPB-10K0-2U1C meets the industry's highest environmental, mechanical and electrical standards. It operates with your USB devices, adapters and cables with top efficiency and safety.

Compact Housing Packs in a Pocket for On-the-Go ChargingAn ideal power solution when you're on the road or stuck somewhere without convenient electricity, the portable battery charger weighs less than one pound. It fits comfortably in your purse, pocket or backpack to keep your phone, tablet, Kindle, AirPods or other mobile device operating when you need it.

Highlights

- Ideal for road trips, hikes, blackouts and other applications without AC power
- USB-A and USB-C ports provide 30W maximum charging power simultaneously
- 10,050mAh of lithium-ion battery capacity is plenty for hours of maximum power draw
- Certified by USB-IF to ensure highest-grade construction and performance
- LED indicators show remaining power bank battery capacity at a glance

Applications

- Charge tablets and other mobile devices while away from home or office
- Maintain your smartphones' battery capacities while camping or hiking
- Keep your mobile devices working during a utility power outage

Package Includes

- UPB-10K0-2U1C 10,050mAh 3-Port Mobile Power Bank USB Battery Charger
- USB-C cable (M/M), 3 ft.
- Owner's manual



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Specifications

OVERVIEW	
UPC Code	037332214201
Product Type	Portable Charger
Charging Form Factor	Portable
Device Compatibility	Phone; Tablet; Amazon Kindle
Country/Region	Global
INPUT	
Nominal Input Voltage(s) Supported	5V DC
Input Plug Type	USB-C (FEMALE)
Input Plug Type Details	USB-A to USB-C cable provided
OUTPUT	
Output Capacity (Watts)	30
Continuous Output Capacity (Watts)	30
Overload Protection	Yes
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
Capacity (Ah)	10.05
POWER	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.0
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	USB C (FEMALE)
Side B - Connector 1	(2) USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Nickel
Connector Style	Straight
USER INTERFACE, ALERTS & CONTROLS	



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

LED Indicators	Blue LED's illuminate to indicate the charging status of the device's battery.
CHARGING	
Number of Charging Ports	2
Total Charging Amps	3A
Total Charging Watts	30
Charging Method	USB
Charging Method Detail	10,050 mAh
Charging Port Type	(2) USB A (FEMALE); USB C (FEMALE)
Charging Ports	(2) 2.4A Quick Charge
Charging Ports Details	USB-C: 5V/3A, 9V/2A, 12V/1.5AUSB-A: 5V/2.4A
Charging Ports / Amps	(2) 2.4A; 3A
Magnetic Charging	No
Wireless Charging	No
Overcharge Protection	Yes
Compatible Devices	Smartphone; Tablet
PHYSICAL	
Color	Black
Material of Construction	ABS
Total Number of Ports	3
Shipping Dimensions (hwd / in.)	1.81 x 9.25 x 4.65
Shipping Dimensions (hwd / cm)	4.60 x 23.50 x 11.81
Shipping Weight (lbs.)	0.72
Shipping Weight (kg)	0.33
Unit Dimensions (hwd / in.)	4.900 x 2.800 x 1.000
Unit Dimensions (hwd / cm)	12.4 x 19.8 x 2.5
Unit Packaging Type	Box
Unit Weight (lbs.)	0.4
Unit Weight (kg)	0.18
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 90% RH, Non-Condensing
Storage Humidity Range	5% to 95% RH, Non-Condensing

FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Yes
Quick Charge Compliant	No
Number of USB Hub Ports	0
Driver Required	No
STANDARDS & COMPLIANCE	
Product Certifications	USB-IF
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[UPB-10K0-2U1C](#)