

Capacitor Kits

Kit #	Description	Capacitance Range	Voltage Range	Features
-------	-------------	-------------------	---------------	----------

Surface Mount Aluminum Electrolytic Kits

**	V-CHIP-KIT1 \$95.00*	Types AVS, AHA & AFC, General Purpose Kit SMT Aluminum Electrolytic Capacitors	10 μ F - 1000 μ F	6.3 to 50 Vdc	20 pcs. each of 21 PNs (420 capacitors)
	V-CHIP-KIT2 \$59.00*	Types AVS, AHA & AFC, General Purpose Kit SMT Aluminum Electrolytic Capacitors	10 μ F - 1000 μ F	6.3 to 50 Vdc	10 pcs. each of 21 PNs (210 capacitors)
**	V-CHIP-KIT4 \$52.00*	Types AFC & AFK, Low [Z], Long Life Kit, 10 mm Max. ht., SMT Aluminum Electrolytic Capacitors	10 μ F - 1000 μ F	10 to 100 Vdc	10 pcs. each of 18 PNs (180 capacitors)
	AVS-KIT1 \$35.00*	Type AVS, Low Cost, General Purpose Kit SMT Aluminum Electrolytic Capacitors	0.1 μ F - 1000 μ F	10 to 50 Vdc	10 pcs. Each of 17 PNs (170 capacitors)
**	AFC-KIT1 \$75.00*	Type AFC, Low [Z], Long Life Kit SMT Aluminum Electrolytic Capacitors	0.1 μ F - 470 μ F	16 to 50 Vdc	20 pcs. Each of 15 PNs (300 capacitors)
	AFK-KIT1 \$45.00*	Type AFK, Low ESR, Low [Z], Long Life Kit 80 Vdc, SMT Aluminum Electrolytic Capacitors	3.3 μ F - 470 μ F	80 Vdc	10 pcs. ea. of 6 PNs and 4 pcs. ea. of 4 PNs (84 caps)
	AFK-KIT2 \$65.00*	Type AFK, Low ESR, Low [Z], Long Life Kit SMT Aluminum Electrolytic Capacitors	10 μ F - 1000 μ F	10 to 100 Vdc	10 pcs. ea. of 13 PNs and 6 pcs. ea. of 9 PNs (184 Caps)
**	AFK-KIT3 \$85.00*	Type AFK, Low ESR, Low [Z], Long Life Kit 100 Vdc, SMT Aluminum Electrolytic Capacitors	22 μ F - 330 μ F	100 Vdc	10 pcs. ea. of 2 PNs and 6 pcs. ea. of 6 PNs (56 Caps)

**KIT IS OBSOLETE

Surface Mount Polymer Aluminum Electrolytic Kits

	ESRD-KIT6 \$28.00*	Solid Polymer Aluminum Electrolytics (7.3x4.3x1.8 mm)	8.2 μ F - 56 μ F	4.0 to 16 Vdc	6 pcs each of 5 PNs (30 capacitors)
	ESRD-KIT9 \$59.00*	Solid Polymer Aluminum Electrolytics (7.3x4.3x3.1 mm)	100 μ F - 220 μ F	2.0 to 6.3 Vdc	6 pcs each of 5 PNs (30 capacitors)
	ESRE-KIT2 \$99.00*	Solid Polymer Aluminum Electrolytics (7.3x4.3x4.2 mm)	100 μ F - 330 μ F	2.0 to 8.0 Vdc	6 pcs each of 7 PNs (42 capacitors)
**	LAB-KIT3 \$455.00*	Large Assortment of ESRD & ESRE Solid Polymer Aluminum Capacitors	8.2 μ F - 270 μ F	2.0 to 16 Vdc	24 pcs each of 17 PNs (408 capacitors)

**KIT IS OBSOLETE

Surface Mount Mica Chip Kits

	MCSK1 \$125.00*	CATV Mica Chips 0805 & 1210 cases	1 pF - 100 pF	100 Vdc	8 pcs. each of 17 PNs (136 capacitors)
	MCSK2 \$135.00*	CATV Mica Chips 0805 & 1210 cases	1 pF - 100 pF	500 Vdc	8 pcs. each of 17 PNs (136 capacitors)
	MCSK3 \$135.00*	RF Microwave, Pulse & Snubber 0805 & 1210 cases	1 pF - 91 pF	100 Vdc	8 pcs. each of 18 PNs (144 capacitors)
	MCSK4 \$165.00*	RF Microwave, Pulse & Snubber 1210 cases	1 pF - 91 pF	500 Vdc	8 pcs. each of 18 PNs (144 capacitors)
	MCSK14 \$185.00*	High Voltage Mica Chip Kit 2220 cases	390 pF - 1000 pF	1000 Vdc	8 pcs. each of 10 PNs (80 capacitors)
	MCSK15 \$175.00*	Low Frequency Filter Mica Chip Kit 0805 & 1210 cases	1 pF - 100 pF	100 Vdc	8 pcs. each of 18 PNs (144 capacitors)

Recommended resale price. If purchased from CDE distributor, your price may vary.

Kit #	Description	Capacitance Range	Voltage Range	Features
-------	-------------	-------------------	---------------	----------

Surface Mount Film Chip Kits

FCA-KIT1 \$30.00*	SMT Acrylic Film Capacitors 0805, 1206, 1210 cases	0.1 μ F - 1.0 μ F	16 Vdc	24 pcs. each of 7 PNs (168 capacitors)
FCN-KIT1 \$36.00*	SMT PEN Film Chip Capacitors 1913 & 2416 cases	0.068 μ F - .47 μ F	16 & 50 Vdc	10 pcs. each of 8 PNs (80 capacitors)
FCN-KIT2 \$46.00*	SMT PEN Film Capacitors 1206 to 3925 cases	0.001 μ F - 1.0 μ F	100 Vdc	10 pcs. each of 10 PNs (100 capacitors)
FCN-KIT3 \$75.00*	SMT PEN Film Capacitors 1913 to 6040 cases	0.001 μ F - 1.0 μ F	250 Vdc	12 pcs. each of 12 PNs (144 capacitors)
FCP-KIT1 \$58.00*	SMT Polyphenylene Sulfide (PPS) Film Chips 0805, 1206, 1210 & 1913 cases	100 pF - 0.1 μ F	50 Vdc	12 pcs. Each of 17 PNs (204 capacitors)
FCP-KIT2 \$39.95*	SMT Polyphenylene Sulfide (PPS) Film Chips 0805, 1206 & 1210	3300 pF - 0.1 μ F	16 Vdc	12 pcs. Each of 12 PNs (144 capacitors)

Mica Kits

MICA-KIT1 \$150.00*	Leaded Mica CD5, CD10, CD15 CD19, CDV19, Most Popular Ratings	5 pF - 1000 pF	300 & 500 Vdc	5 pcs. each of 48 PNs (240 capacitors)
MICA-KIT2 \$165.00*	Leaded Mica, CD5 Series Various Tolerances	1 pF - 390 pF	50, 100 & 300 Vdc	5 pcs. each of 57 PNs (285 capacitors)
MICA-KIT3 498.00*	Leaded Mica, CD6 & CD7 Series ± 0.05 pf, $\pm 1\%$, $\pm 2\%$ Tolerances	1 pF - 1300 pF	100 & 500 Vdc	5 pcs. each of 48 PNs (240 capacitors)
MICA-KIT4 \$398.00*	Leaded Mica, CD15 & CD19 Series $\pm 5\%$ Tolerance	10 pF - 7500 pF	500 Vdc	5 pcs each of 72 PNs (360 capacitors)
MICA-KIT5 \$75.00*	Leaded Mica Snubber Kit, CD16, CDV16, CD30, CDV30, $\pm 5\%$ Tolerance	100 pF - 10000 pF	500 & 1000 Vdc	12 Part Numbers (64 capacitors)
MICA-KIT6 \$39.95*	Leaded Mica, CD4 Series High Frequency for Flat Insertion Loss thru 1 GHz	2 pF - 1500 pF	100 & 500 Vdc	10 Part Numbers (67 capacitors)

Recommended resale price. If purchased from CDE distributor, your price may vary.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cornell Dubilier:](#)

[MCSK4](#)