

EP Series

Plugs for Threaded Connectors



The EP series plugs for threaded connectors are designed for easy application and removal in areas not accessible. They can be installed to fit threaded or smooth cylindrical surfaces.

Material: Low-Density Polyethylene
Standard Color: Yellow

Diagram

Item #	Dim A (IN)	Dim B (IN)	Dim C (IN)	Dim D (IN)	To Plug Nominal Thread Size IN		
EP-8	0.483	0.67	0.63	0.41	1/2-28	+ Available Options	Request Sample
EP-10	0.595	0.75	0.63	0.53	5/8-24	+ Available Options	Request Sample
EP-12	0.715	0.86	0.63	0.66	3/4-20	+ Available Options	Request Sample
EP-14	0.845	1.03	0.63	0.79	7/8-20	+ Available Options	Request Sample
EP-16	0.963	1.12	0.63	0.89	1-20	+ Available Options	Request Sample
EP-18	1.088	1.25	0.63	1.03	1-1/8-18	+ Available Options	Request Sample
EP-20	1.215	1.40	0.63	1.15	1-1/4-18	+ Available Options	Request Sample

Item #	Dim A (IN)	Dim B (IN)	Dim C (IN)	Dim D (IN)	To Plug Nominal Thread Size IN		
EP-22	1.340	1.50	0.63	1.27	1-3/8-18	+ Available Options	Request Sample
EP-24	1.460	1.64	0.55	1.39	1-1/2-18	+ Available Options	Request Sample
EP-25	1.580	1.81	0.63	1.54	1-5/8-18	+ Available Options	Request Sample
EP-28	1.718	1.87	0.63	1.68	1-3/4-18	+ Available Options	Request Sample
EP-32	1.970	2.13	0.63	1.89	2-18	+ Available Options	Request Sample
EP-36	2.210	2.34	0.63	2.14	2-1/4-16	+ Available Options	Request Sample
EP-40	2.450	2.60	0.63	2.38	2-1/2-16	+ Available Options	Request Sample
EP-44	2.700	2.88	0.63	2.63	2-3/4 - 16	+ Available Options	Request Sample
MS-48-Y	2.950	3.12	0.63	2.88	3-16	+ Available Options	Request Sample

Diagram



[Shopping Cart \(/cart\)](#) [Contact Us \(/contact-us\)](#) [About Us \(/about\)](#) [Awards \(/awards\)](#) [Returns \(/returns\)](#) [Privacy \(/privacy\)](#) [Terms & Conditions \(/terms-conditions\)](#)

Quick Links: [About Us \(/about\)](#) [Military & NAS Specifications \(/mil-nas-spec\)](#) [Quality Certifications & Regulatory Info \(/quality\)](#) [Cross Reference \(/cross-reference\)](#)

Products [Plastic Caps \(/caps\)](#) [Plastic Plugs \(/plugs\)](#) [Masking \(/masking-parts\)](#) [Tubing, Netting, & Containers \(/tubing-netting-containers\)](#) [More Product Protection \(/more\)](#) [Hose Guard / Spiral Wrap \(/hoseguards\)](#) [Tri-Star Thread Protectors \(http://tristarprotector.com/\)](#) [Evergreen Labware \(http://www.evergreensci.com/\)](#)

Materials [Polyethylene \(/polyethylene\)](#) [Vinyl \(/vinyl\)](#) [Silicone \(/silicone\)](#) [Molded Rubber \(/rubber\)](#) [PETG \(/petg\)](#) [Additional Materials \(/additional-materials\)](#) [Material Specification \(/material-spec\)](#)

Applications [Masking \(/masking\)](#) [Medical \(/medical\)](#) [Evergreen Labware \(http://www.evergreensci.com/\)](#) [Thread & Flange Protection \(/thread-and-flange\)](#) [Tri-Star Thread Protectors \(http://tristarprotector.com/\)](#) [Automotive \(/automotive\)](#) [Electronics \(/electronics\)](#) [Hydraulics \(/hydraulics\)](#) [Compressed Gas \(/compressed-gas\)](#) [Packaging & Netting \(/packaging-netting\)](#) [Aviation \(/aviation\)](#) [Hose Guard / Spiral Wrap \(/hoseguard\)](#)

Custom Parts [Design A Part \(/design-part\)](#) [Molding Capabilities \(/molding\)](#)

Service & Support [Find a Sales Representative \(/sales-reps\)](#) [Learning Center \(/learning-center\)](#) [Download Catalog \(/catalogs\)](#) [Request a Quote \(/form/quote\)](#) [Contact Us \(/contact-us\)](#) [Quality \(/quality\)](#) [Patents \(/patents\)](#) [Press Room \(/press-room\)](#) [Awards \(/awards\)](#) [Join Our Team \(/join-our-team\)](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Caplugs:](#)

[EP-24](#)