

CRYSTEK
MICROWAVE
A DIVISION OF CRYSTEK CORPORATION

Low Pass Filter
50Ω SMA
7th Order




Part Number: CLPFL-1600

Low Pass Range
DC to 1600 MHz



Schematic



Features:


- 7th Order Butterworth Response
- 50Ω SMA Connectors

Applications:

- Test Equipment
- Lab Use

Maximum Ratings:

- +36dBm (4 Watts)
- Operating Temperature: -40°C to 85°C
- Storage Temperature: -55°C to 100°C



Crystek's new line of Low Pass Filters are designed in a rugged SMA housing. This filter line has excellent out-of-band rejection. Designed for Test Equipment and General Lab Use.





Rev C


Page 1 of 3



CRYSTEK
CORPORATION

12730 COMMONWEALTH DRIVE • FORT MYERS, FLORIDA 33913
PHONE: 239-561-3311 • 800-237-3061
FAX: 239-561-1025 • WWW.CRYSTEK.COM





FREQ (MHz)	INSERTION LOSS (dB)	Male Return Loss (dB)	Female Return Loss (dB)
50.000	0.02	32.19	32.15
249.500	0.15	20.40	20.37
449.000	0.22	17.66	17.56
648.500	0.23	18.65	18.52
848.000	0.24	27.72	27.30
947.750	0.28	32.83	31.08
1047.500	0.34	19.84	19.62
1247.000	0.66	10.61	10.52
1446.500	1.44	6.05	6.01
1546.250	2.52	4.54	4.54
1646.000	3.59	3.37	3.41
1845.500	7.35	1.80	1.89
2045.000	12.23	1.03	1.04
2244.500	18.08	0.70	0.63
2444.000	26.50	0.53	0.42
2643.500	38.90	0.42	0.33
3042.500	38.88	0.31	0.33
3341.750	36.18	0.26	0.40
3641.000	36.77	0.18	0.45
4040.000	34.76	0.19	0.42
4339.250	34.36	0.31	0.39
4638.500	35.08	0.39	0.42
5037.500	35.48	0.46	0.53
5336.750	35.30	0.47	0.61
5636.000	35.47	0.47	0.65
6035.000	35.91	0.45	0.68
6334.250	34.91	0.42	0.69
6633.500	34.34	0.37	0.67
7032.500	35.40	0.30	0.60
7331.750	33.58	0.26	0.50
7631.000	32.42	0.21	0.46
8030.000	28.40	0.19	0.47
8329.250	27.88	0.21	0.49
8628.500	27.89	0.38	0.49
9027.500	26.68	0.70	0.44
9326.750	24.10	1.01	0.42
9626.000	21.88	1.29	0.43
9925.250	17.44	1.75	0.65

Product Control:

Crystek Part Number:	CLPFL-1600	Release Date:	04-Aug-2015
Revision Level:	C	Responsible:	K. Piotrowicz

Rev C

Page 3 of 3



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Crystek:](#)

[CLPFL-1600](#)