


0.5mm Pitch

SERIES

6284


0.5mmピッチ Non-ZIF RA SMT 両面接点

0.5mmPitch LIF RA SMT Dual-sided contact




極数 NO. OF POS.	A	B	C
5	2.0	4.4	3.1
6	2.5	4.9	3.6
7	3.0	5.4	4.1
8	3.5	5.9	4.6
9	4.0	6.4	5.1
10	4.5	6.9	5.6
11	5.0	7.4	6.1
12	5.5	7.9	6.6
13	6.0	8.4	7.1
14	6.5	8.9	7.6
15	7.0	9.4	8.1
16	7.5	9.9	8.6
17	8.0	10.4	9.1
18	8.5	10.9	9.6
19	9.0	11.4	10.1
20	9.5	11.9	10.6
21	10.0	12.4	11.1
22	10.5	12.9	11.6
23	11.0	13.4	12.1
24	11.5	13.9	12.6
25	12.0	14.4	13.1
26	12.5	14.9	13.6
27	13.0	15.4	14.1
28	13.5	15.9	14.6
29	14.0	16.4	15.1
30	14.5	16.9	15.6

● 5 to 24 Pos.



● 25 to 30 Pos.



極数 NO. OF POS.	J	K	L
5	7.5		16
6	7.5		16
7	7.5		16
8	7.5		16
9	11.5		24
10	11.5		24
11	11.5		24
12	11.5		24
13	11.5		24
14	11.5		24
15	11.5		24
16	11.5		24
17	11.5		24
18	11.5		24
19	11.5		24
20	11.5		24
21	11.5		24
22	11.5		24
23	11.5		24
24	11.5		24
25	14.2	28.4	32
26	14.2	28.4	32
27	14.2	28.4	32
28	14.2	28.4	32
29	14.2	28.4	32
30	14.2	28.4	32

注文コード ORDERING CODE
04 6284 0XX 00X XXX+

RoHS 対応品
RoHS Compliant Product

800+: スズ銅めっき Sn-Cu Plated
846+: 金めっき Au Plated

1: 5-10 Positions
2: 11-30 Positions

極数 NUMBER OF POSITIONS

生産対応可能極数については、営業部にご確認願います。

Feel free to contact our sales department for available numbers of positions.

梱包数量 4000個/リール
PACKING QUANTITY: 4000/Reel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kyocera:

046284016002846+	046284005001846+	046284011002846+	046284024002800+	046284020002800+
046284005001800+	046284006001800+	046284012002846+	046284015002846+	046284022002846+
046284007001846+	046284010001846+	046284024002846+	046284017002846+	046284018002846+
046284014002846+	046284008001846+	046284009001846+	046284026002846+	046284020002846+
046284006001846+	046284030002800+	046284030002846+	046284021002846+	046284008001800+
046284012001800+	046284012002800+	046284015002800+	046284018001800+	046284018002800+
046284024001846+	046284026001846+	046284014001846+	046284020001846+	046284010001800+
046284010801846+	046284011001846+	046284017001800+	046284009001800+	046284015001846+
046284018001846+	046284020001800+	046284013002800+	046284007001800+	046284011002800+
046284012001846+	046284016001800+	046284014002800+	046284015001800+	046284021001800+
046284024001800+	046284016001846+	046284014001800+	046284021001846+	046284021002800+
046284026001800+	046284026002800+	046284016002800+	046284030001846+	046284011001800+
046284017001846+	046284017002800+	046284030001800+		