


ODU AMC[®] SERIES T IN-LINE RECEPTACLE FOR BACKSHELL, SHELL SIZE 09, IP6K9K, 10 CONTACTS, A (LIGHT BROWN) KEY




- **Part number** KBTAAT0-E010SN-0000
- **Type of connector** In-line receptacle for backshell
- **Size** Shell size 09
- **Number of contacts** 10
- **Keying** A (light brown)
- **Cable diameter** 3 - 7.6 mm



DIMENSIONS:



POSITIONS: 10 positions



CODING: A



Contact Insert Description

Number of contacts	10
Contact type	Sockets
Contact diameter	0.76 mm
Insulator material	PEEK
Wire cross section	AWG 22-26
Termination type	Crimp
Contact size	#22D

Reverse gender on request

ODU AMC[®] SERIES T IN-LINE RECEPTACLE FOR BACKSHELL, SHELL SIZE 09, IP6K9K, 10 CONTACTS, A (LIGHT BROWN) KEY



Technical information

Nominal current single contact	5 A	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Test voltage	0.75 kV AC	EIA-364-20F:2019-02

All shown connectors are rated to a safety extra low voltage (SELV) of less than 50 V AC / 75 V DC, according to IEC 61140:2016 (VDE 0140-1:2016) Protection against electric shock - Common aspects for installation and equipment. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid. Warning: Danger to life for operating voltages above 50 V AC / 120 V DC!

Mechanical and Environmental data

Degree of protection*	IP6K9K
Operating temperature	-65°C - 175°C
Mating cycles	500
*mated	

Material and Surface Treatments

Housing	Aluminum with tin-nickel finish
Contact	Cu-alloy with gold finish

General information

All shown connectors are defined without breaking capacity (COC) according to IEC 61984:2008 (VDE 0627:2009).

The respective selected ODU connectors with data transfer functionality can transmit common data transmission such as HDMI[®] 2.0, USB[®] 3.2 Gen 1x1, FireWire[®] and eSATA[®], but they are not HDMI[®]-, USB[®]-, FireWire[®]- and eSATA[®]-standard connectors.

ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ODU USA:

[KBTAAT0-E010SN-0000](#)