


SERIES


SERIES 6296

0.3mmPitch RA SMT Bottom contact One-touch lock



ガイド有り
WITH GUIDE

04 6296 0XX 230 XXX +






ガイド無し
NO GUIDE

04 6296 0XX 231 XXX +


DETAIL "L"

傳 數 NO. OF POS.	A	B	C	D
11	3.0	2.4	5.2	3.7
13	3.6	3.0	5.8	4.3
15	4.2	3.6	6.4	4.9
17	4.8	4.2	7.0	5.5
19	5.4	4.8	7.6	6.1
21	6.0	5.4	8.2	6.7
23	6.6	6.0	8.8	7.3
25	7.2	6.6	9.4	7.9
27	7.8	7.2	10.0	8.5
29	8.4	7.8	10.6	9.1
31	9.0	8.4	11.2	9.7
33	9.6	9.0	11.8	10.3
35	10.2	9.6	12.4	10.9
37	10.8	10.2	13.0	11.5
39	11.4	10.8	13.6	12.1
41	12.0	11.4	14.2	12.7
43	12.6	12.0	14.8	13.3
45	13.2	12.6	15.4	13.9
47	13.8	13.2	16.0	14.5
49	14.4	13.8	16.6	15.1
51	15.0	14.4	17.2	15.7
61	18.0	17.4	20.2	18.7



デーハ'一部をオーバーラップさせる事により
図全体の幅が狭くなり、傾くおそれあり

For prevention against an open circuit in being bent, the tapered areas shall be laid as indicated.

**注文コード ORDERING CODE**

04 6296 0XX 93X XXX+

RoHS 対応品

RoHS Compliant Product

- めっきコード Plating code
- 846：金めっき Au Plated

・ FPCガイド FPC Guide

0 : ガイド有り 0 : With guide

1 : ガイド無し 0 : No guide

- 極数 NUMBER OF POSITIONS

傳數 NO. OF POS.	A	B	C
11	7.5	-	16.0
13	7.5	-	16.0
15	7.5	-	16.0
17	7.5	-	16.0
19	11.5	-	24.0
21	11.5	-	24.0
23	11.5	-	24.0
25	11.5	-	24.0
27	11.5	-	24.0
29	11.5	-	24.0
31	11.5	-	24.0
33	11.5	-	24.0
35	11.5	-	24.0
37	11.5	-	24.0
39	11.5	-	24.0
41	11.5	-	24.0
43	11.5	-	24.0
45	11.5	-	24.0
47	11.5	-	24.0
49	11.5	-	24.0
51	11.5	-	24.0
61	14.2	28.4	32.0

生産対応可能極数については、営業部にご確認願います。

Feel free to contact our sales department for available numbers of positions.

梱包数量 2000個/リール
PACKING QUANTITY : 2000/Reel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kyocera:

<u>046296011930846+</u>	<u>046296015930846+</u>	<u>046296015931846+</u>	<u>046296019930846+</u>	<u>046296021930846+</u>
<u>046296021931846+</u>	<u>046296041931846+</u>	<u>046296043931846+</u>	<u>046296045930846+</u>	<u>046296051930846+</u>
<u>046296035930846+</u>	<u>046296035931846+</u>	<u>046296037931846+</u>	<u>046296039931846+</u>	<u>046296031930846+</u>
<u>046296031931846+</u>	<u>046296033930846+</u>	<u>046296033931846+</u>	<u>046296027931846+</u>	