


ILLUMINATED SWITCH TL(L)A(G)-7 SERIES

Tact Switch
Illuminated




ILLUMINATED SWITCH

TLLA-72



TLLAG-7



LED Color Options:

Part No.	Color	Dominant Wavelength λ_D Typ.(nm)	Luminous Intensity I_v (mcd)		Forward Voltage V_f (V)		View Angle $2\theta_{1/2}$ (Degree)	
			Typ.		Typ.	Max.	A	B
			A	B				
B	Blue	470	70	1100	3.0	3.6	140°	30°
PG	Pure Gree	520	160	2500	3.2	3.6		
G	Yellow Green	570	30	550	2.0	2.3		
Y	Yellow	590	60	1500	2.0	2.3		
A	Soft Orange	605	50	1500	2.0	2.3		
R	Deep Red	640	25	800	2.0	2.3		
W	Cold White	X:0.30 / Y:0.30	350	550	3.0	3.6		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diptronics:

[TLLA-72BAG-Q-B](#) [TLLA-72BR-R1SH1-V-A](#) [TLLA-73BB-R1KH0-V-A](#) [TLLA-72BG-R1SH4-V-A](#) [TLLA-72BB-Q-A](#)
[TLLA-72BGR-R1T-V-A](#) [TLLAG-72BB-R1SH0-V-A](#) [TLLA-72BAG-Q-A](#) [TLLA-72BB-R1SH0-V-A](#) [TLLA-73BB-Q-A](#) [TLLA-](#)
[72APG-R1SH1-V-A](#) [TLLA-72BB-R2KH1-V-A](#) [TLLA-72BGY-R1SH3-V-A](#) [TLLA-72BR-Q-A](#) [TLLA-72BPG-R1T-V-A](#)
[TLLA-72BGY-Q-A](#) [TLLA-72BA-R1SH0-V-A](#) [TLLA-73BB-R1SH4-V-A](#) [TLLA-72BGY-R1SH1-V-A](#) [TLLA-72BAG-R1T-V-A](#)
[TLLAG-72BB-R1SH4-V-A](#) [TLLA-72BB-R1KH0-V-A](#) [TLLA-72BRB-R1SH1-V-A](#) [TLLA-72BB-R1KH1-V-A](#) [TLLA-72BG-](#)
[Q-A](#) [TLLA-72BGY-R1T-V-A](#) [TLLA-72BB-R2KH2-V-A](#) [TLLA-72BG-R1SH0-V-A](#) [TLLA-72BB-R1KH4-V-A](#) [TLLA-](#)
[72AAPG-R1KH1-V-A](#) [TLLA-72BG-R1KH7-V-A](#) [TLLA-72BY-R2T-V-A](#) [TLLA-73BG-R1SH4-V-A](#) [TLLA-73BG-Q-A](#) [TLLA-](#)
[72BGY-Q-B](#) [TLLA-72BAW-Q-B](#) [TLLA-72BAPG-R1T-V-A](#) [TLLA-72BG-R1T-V-A](#) [TLLA-72BPG-R1KH1-V-A](#) [TLLA-](#)
[72BB-R3T-V-A](#) [TLLA-72BPG-R2KH1-V-A](#) [TLLA-72BGY-R1KH1-V-A](#) [TLLA-72BB-R1KH1-V-B](#) [TLLA-72BB-R2T-V-A](#)
[TLLA-72BB-R1SH3-V-A](#) [TLLA-72BG-R1SHB-V-A](#) [TLLA-72BGY-R2T-V-A](#) [TLLA-72AG-Q-A](#) [TLLAG-72BRG-R2SHB-V-](#)
[A](#) [TLLA-72AB-R1T-V-A](#) [TLLA-72BGY-R1KH0-V-A](#) [TLLA-72BAPG-R1KHB-V-A](#) [TLLAG-72BGY-Q-A](#) [TLLA-72BB-](#)
[R1SH4-V-A](#) [TLLA-72BG-R1KH1-V-A](#) [TLLA-72AB-Q-A](#) [TLLA-72BRG-R1T-V-A](#) [TLLA-72BB-R1T-V-A](#) [TLLA-72BRG-](#)
[R1T-V-B](#) [TLLA-72AG-R1SH0-V-A](#)