


CW
INDUSTRIES



Your Source for Custom-Designed Switches, Connectors & Assemblies




SWITCHES



An ISO Company that
Delivers World Class Quality

**ROCKER, PUSHBUTTON
& TOGGLE SWITCHES**

ROCKER



GRS-4000

8A, 13A, 16A
SPST, SPDT, DPST, DPDT
Maintained, Mom, Center Off
.508" X .756" Panel Opening




GRL-4000

8A, 13A, 16A - Illuminated
SPST, SPDT, DPST, DPDT
Maintained
.508" X .756" Panel Opening




GRS-2000

8A, 13A, 16A
SPST, SPDT
Maintained, Mom, Center Off
.550" X 1.125" or
.480" X 1.072" Opening



GRL-2000

8A, 13A, 16A - Illuminated
SPST, SPDT
Maintained
.550" X 1.125" Panel Opening



GR-2000

8A, 13A, 16A
DPST, DPDT
Maintained, Mom, Center Off
.872" X 1.071" Panel Opening



GRS-6000

40A 12VDC
DPDT
Reversing Switch
.948" X 1.580" Panel Opening



GRS-2000-5000

16 Amps
SPST, SPDT—Maintained
Colors and Markings available
.550" X 1.125" or .480" X 1.072"



GRS-4000-5000

16 Amps
SPST, SPDT, DPST, DPDT
Color and Markings available
.508" X .756" Panel Opening

ROCKER



GRB049

10 Amps
SPST, SPDT, DPDT
Maintained
.717" Panel Opening



GRB066

16 Amps—Illuminated / Non
SPST, SPDT
Maintained, Mom, Center Off
.508" X .756" Panel Opening



GRB293

10A 125VAC
SPST, SPDT—Maintained
Illuminated / Non
.866 with Keyway



GRB130

10 Amps
SPST, SPDT, DPDT
Maintained
.717" Panel Opening
with Keyway



GRB136

10 Amps
SPST, SPDT, DPDT
Maintained
.717" Panel Opening
with Keyway



GRB213

6 Amps
SPST, SPDT, DPST, DPDT
Maintained
.480" with 2 flats



GRB243

8 Amps
SPST
Maintained, Momentary
.276" X .756" Panel Opening



GC-509

3A 125VAC
Sequencing Switch
SPDT 3 POS ON-OFF-[ON]
.508" X .756" Panel Opening

ROCKER



GRB066X8

16A 125VAC IP65
SPST, SPDT—Maintained
Illuminated / Non
.508" X .780" Panel Opening



GRB112X8

16 A 125VAC IP65
SPST, SPDT
Maintained, Mom, Center Off
.795" with Keyway



GRB244X8

16A 125VAC IP65
DPST, DPDT
Maintained, Center Off
.795" with Keyway



GRB203X8

16A 125VAC IP65
SPST, SPDT—Maintained
Illuminated / Non
.945" with Keyway



GRB263

16A 125VAC
SPST, SPDT - Illuminated
Maintained, Mom, Center Off
.835" X 1.44" Panel Opening



GRB292

21A 14VDC IP67
SPST, SPDT, DPST, DPDT
Maintained, Mom, Center Off
.835" X 1.44" Panel Opening



GRB1X4 Series

25A 12VDC IP68
SPST, SPDT
Maintained, Mom, Center Off
.831" X 1.457" Panel Opening



GRB2X4 Series

25A 12VDC IP68
DPST, DPDT
Maintained, Mom, Center Off
.831" X 1.457" Panel Opening

ROCKER

GRB070X8

16 A 125VAC IP65
 SPST, SPDT - Illuminated / Non
 Maintained, Mom, Center Off
 .441" X 1.189" Panel Opening


GRB238X8

16A 125VAC IP65
 SPST, SPDT - Illuminated/ Non
 Maintained, Mom, Center Off
 .543" X 1.087" Panel Opening


GRB258X

20A 125VAC IP56
 SPST, SPDT - Illuminated / Non
 Maintained, Mom, Center Off
 .602" X 1.449" Panel Opening


GRB260X

20A 125VAC IP56
 SPST, SPDT, DPST, DPDT
 Maintained, Mom, Center Off
 .835" X 1.441" Panel Opening


GRB263X0

16A 125VAC IP56
 SPST, SPDT
 Maintained, Mom, Center Off
 .835" X 1.441" Panel Opening


GRB271

20A 125VAC IP66
 SPST, SPDT, DPST, DPDT
 Maintained, Mom, Center Off
 .835" X 1.441" Panel Opening


GRB285X8

20A 125VAC IP65
 DPST, DPDT-Illuminated /Non
 Maintained
 .874" X 1.189" Panel Opening


GRB278X8

20A 14VDC IP65
 SPST, SPDT - Illuminated / Non
 Maintained, Momentary
 .457" X .917" Panel Opening

TOGGLE

GTB1B11

IP68
 12A 125VAC /250VAC
 SPDT ON-OFF-ON
 .472" with Key Way


GTB1B17

IP68
 12A 125VAC /250VAC
 SPDT (ON)-OFF-(ON)
 .472" with Key Way


GTB2B12

IP68
 12A 125VAC /250VAC
 SPST OFF-ON
 .472" with Key Way


GTB2B13

IP68
 12A 125VAC /250VAC
 SPDT ON-ON
 .472" with Key Way


GTB2B18


IP68
 12A 125VAC /250VAC
 SPDT (ON)-ON
 .472" with Key Way


GTB3B11

IP68
 12A 125VAC /250VAC
 DPDT ON-OFF-ON
 .472" with Key Way


GTB3B17

IP68
 12A 125VAC /250VAC
 DPDT (ON)-OFF-(ON)
 .472" with Key Way


GTB4B12

IP68
 12A 125VAC /250VAC
 DPST OFF-ON
 .472" with Key Way

TOGGLE

GTB4B13

IP68
 12A 125VAC /250VAC
 DPDT ON-ON
 .472" with Key Way


GTB4B18

IP68
 12A 125VAC /250VAC
 DPDT (ON)-ON
 .472" with Key Way


GTS 447

16A 277VAC IP56
 SPST, SPDT
 Maintained, Mom, Center Off
 .480" with Key Way


GTS 448

16A 277VAC IP56
 DPST, DPDT
 Maintained, Mom, Center Off
 .480" with Key Way

**Other Products
 from CW Industries:**

- Slide Switches
- IDC Connectors
- High Density Rectangular Connectors
- Custom Products

PUSH BUTTON

GPB553X2

10A 14VDC IP65
 SPST, SPDT - Illuminated / Non
 Maintained, Momentary
 .866" Panel Opening


GPB001

6A 125VAC
 2P, 3P, SPST, SPDT
 Maintained, Momentary
 .244" panel Opening


GPB023

3A 125VAC
 SPST
 Maintained, Momentary
 .480" Panel Opening


GPB024

3A 125VAC
 SPST
 Momentary
 .283" Panel Opening


GPB040

3A 125VAC
 SPST
 Maintained, Momentary
 .480" Panel Opening


GPB081

0.5A 125VAC
 SPST
 Momentary
 .205" Panel Opening


GPB502

3A 125VAC
 SPST, SPDT
 Momentary
 .500" Panel Opening


GC536

3A 14VDC
 SPDT - Maintained, Mom.
 PCB, Plug In, Wire Lead
 Op Temp - 105 Degrees C

PUSH BUTTON

GPB507

6A 125VAC
 SPST
 Momentary
 .630" Panel Opening


GPB508

3A 125VAC
 SPST-Illuminated / Non
 Maintained, Momentary
 .630" with Two Flats


GPB510

3A 125VAC
 SPST
 Momentary
 .500" with One Flat


GPB554

6A 14VDC
 SPST - Illuminated / Non
 Maintained, Momentary
 .476" with Key Way


GPB526

16A 125VAC IP56
 SPST, SPDT - Illuminated / Non
 Maintained
 .543" X 1.087" Panel Opening


GPB527X2

10A 125VAC IP65
 SPST, DPST, Illuminated / Non
 Maintained, Momentary
 .795" with Key Way


GPB556

400mA 32VAC IP67
 SPST, SPDT - Illuminated /
 Non-Momentary .472"
 with Two Flats


PUSH BUTTON

GPBS800L

0.1A 30VDC
 DPDT ON-ON
 PCB Mount
 8.0 X 8.0 mm


GPBS800N

0.1A 30VDC
 DPDT ON-(ON)
 PCB Mount
 8.0 X 8.0 mm


GPBS850L

0.3A 30VDC
 DPDT ON-ON
 PCB Mount
 8.5 X 8.5 mm


GPBS850N

0.3A 30VDC
 DPDT ON-ON
 PCB Mount
 8.5 X 8.5 mm


GPTS203211B

1A 30VDC
 SPST ON - OFF
 PCB Mount Right Angle
 12.0 X 12.0 mm


GPTS203212B

1A 30VDC
 SPST ON-OFF
 PCB Mount Straight
 12.0 X 12.0 mm


GPTS203312B

1A 30VDC
 SPDT ON-OFF-ON
 PCB Mount Straight
 12.0 X 12.0 mm

To Access Prints, Data Sheets, Full Product Information and Options:

Go to: www.cwind.com

Search By: Item Number

Type in: Product Series Number

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[GPTS203312B](#) [GPB507A05BG](#)