


KTQ87/mITX



EMBEDDED Mini-ITX MOTHERBOARD WITH Intel® Q87 CHIPSET AND 4th GEN Intel® I7/I5/I3 DUAL AND QUAD CORE CPUS


- ▶ 4th Generation Intel® 22nm Dual and Quad Core i7, i5, i3, Pentium & Celeron® CPUs with Intel® Q87 Lynx Point PCH
- ▶ long term available Embedded mITX motherboard
- ▶ high performance CPU, graphics, and media performance supporting 3 independent displays pipes
- ▶ graphics APIs DirectX 11.1, OpenGL 4.x, OpenCL 1.2

POSSIBILITIES START HERE



KTQ87/mITX

- **Gaming/POS/POI:** High graphics and CPU performance, multi display support
- **Medical:** High Graphics performance & longevity
- **Industrial Automation:** Wide range of I/Os & longevity
- **Future-oriented Devices** Due to Display Port and mSATA/compact SSD support



► TECHNICAL INFORMATION

FEATURES	KTQ87 mITX Desktop Motherboards
FORM FACTOR	mini-ITX 170 x 170 mm (6.7" x 6.7")
CPU	Intel® Core i7/i5/i3 2C/4C CPU clock up to 3.1 GHz
GRAPHICS	Integrated into CPU with GT1 or GT2 depending on CPU type
GRAPHIC INTERFACE	3x Display Port revision 1.2 in Rear IO
MEMORY	Up to 8 GByte DDR3L/DDR3, 2x (max. 16 GByte), PC3-10600/PC3-12800 support
CHIPSET	Intel® Embedded Q87
FRONT SIDE BUS	DMI 2.0 support, four lanes in each direction, up to 20 Gb/s each direction, full duplex, DMI interface to PCH is supported
SATA	5x SATA interfaces SATA 1.5/3/6Gbit/s w. RAID 0/1/5/10
USB	4x USB 3.0 & 10 USB 2.0. (4x USB3.0/USB2.0 Rear IO, 4x USB2.0 Internal Header, USB2.0 mPCIe, USB2.0 mSATA)
AUDIO	HD Audio codec VT1708S supporting 7.1 channel surround sound
ETHERNET	2x Intel Gigabit-LAN, one LAN controller supporting Intel® AMT 9.0
AVAILABLE I/OS	PCIe x16 socket with Gen3 and Gen2 support, 1x Mini-PCIe, 1x mSATA 1.5/3/6Gbit/s, 2x COM (RS232)
REAR I/O	Audio stacked 2x3 mini Jack tower, 4x USB, 3x Display port, 2x RJ45 LAN
SPECIAL FEATURE	AMT 9.0, TPM 1.2, Intel® AES security, Kontron embedded feature connector with ADC, DAC up to 160 GPIO
OS SUPPORT	Win7, Win8 WES8, WES7, Linux, VxWorks
TEMPERATURE	Operating 0 °C to 50 °C (32 °F to 122 °F)
ADDITIONAL	Up to 7 years availability

► ORDERING INFORMATION

ARTICLE	PART NO.		DESCRIPTION
KTQ87/mITX	810580-4500		Q87, mITX, 4x USB 3.0/2.0 ports in Rear-IO, 5x 3/6Gb/s SATA with RAID 0,1,5 & 10, 2x GByte LAN one supporting AMT 9.0, 3x Display Ports
CPUS			
CPU, CORE i5	1054-9757		CPU, Core I5-4570S GT2 2.9G 4C 6M LGA1150
CPU, CORE i7	1054-9752		CPU, Core I7-4770S GT2 3.1G 4C 8M LGA1150
Further CPUs will be defined in near future.			
RECOMMENDED MEMORY MODULES	NEW SKU 04/16*	OLD SKU	SKU NAME**
	1060-2492	1054-3702	DDR3-1333 DIMM 2 GByte
	1060-2494	1054-3703	DDR3-1333 DIMM 4 GByte
	1060-2496	1054-3704	DDR3-1333 DIMM 8 GByte
	1060-2498	1054-3707	DDR3-1600 DIMM 2 GByte
	1060-2500	1054-3708	DDR3-1600 DIMM 4 GByte
	1060-2488	1052-5601	DDR3-1600 DIMM 8 GByte

*SKU changes were caused by administrative issues only, no hardware changes.

**Named are always the min. requirements, the shipped memory can fulfill a higher performance level

► CORPORATE OFFICES

EUROPE, MIDDLE EAST & AFRICA

Lise-Meitner-Str. 3-5
86156 Augsburg
Germany
Tel.: + 49 821 4086 0
Fax: + 49 821 4086 111
info@kontron.com

NORTH AMERICA

14118 Stowe Drive
Poway, CA 92064-7147
USA
Tel.: + 1 888 294 4558
Fax: + 1 858 677 0898
info@us.kontron.com

ASIA PACIFIC

1-2F, 10 Building, No. 8 Liangshuihe 2nd Street,
Economical & Technological Development Zone,
Beijing, 100176, P.R.China
Tel.: +86 10 63751188
Fax: +86 10 83682438
info@kontron.cn

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kontron:](#)

[810550-4500](#) [810554-4500](#) [810580-4500](#) [810551-4500](#) [810552-4500](#) [810553-4500](#)