



PART NUMBER	"L" ±.010 (±0.25)	"A" REF.
LEDS2M-120-01	.12 (3.1)	.08 (2.0)
LEDS2M-140-01	.14 (3.6)	
LEDS2M-160-01	.16 (4.1)	
LEDS2M-180-01	.18 (4.5)	
LEDS2M-200-01	.20 (5.1)	
LEDS2M-220-01	.22 (5.6)	
LEDS2M-240-01	.24 (6.1)	.20 (5.1)
LEDS2M-250-01	.25 (6.4)	
LEDS2M-260-01	.26 (6.6)	
LEDS2M-280-01	.28 (7.1)	
LEDS2M-300-01	.30 (7.8)	
LEDS2M-320-01	.32 (8.1)	
LEDS2M-340-01	.34 (8.6)	.33 (8.4)
LEDS2M-360-01	.36 (9.1)	
LEDS2M-380-01	.38 (9.7)	
LEDS2M-400-01	.40 (10.2)	
LEDS2M-420-01	.42 (10.7)	
LEDS2M-440-01	.44 (11.2)	
LEDS2M-450-01	.45 (11.4)	.45 (11.4)
LEDS2M-460-01	.46 (11.7)	
LEDS2M-500-01	.50 (12.7)	.58 (14.7)
LEDS2M-550-01	.55 (14.0)	
LEDS2M-600-01	.60 (15.2)	.70 (17.8)
LEDS2M-650-01	.65 (16.5)	
LEDS2M-750-01	.75 (19.1)	
LEDS2M-850-01	.85 (21.6)	
LEDS2M-900-01	.90 (22.9)	

NOTES:

1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01).
COLOR: NATURAL,
BLACK AVAILABLE BY SPECIAL ORDER.
2. FOR T-1 3/4 LED'S.

H	SEE CO 200651 FOR CHANGES	SK 04.04.11	TITLE: LED SPACER	DWG IN IN (MM)			
G	SEE CO 200649 FOR CHANGES	SK 04.01.11					
F	SEE ECN #1168 FOR CHANGES	SK 05.19.06					
E	SEE ECN #892 FOR CHANGES	SM 12.14.04					
D	SEE ECN #547 FOR CHANGES	SM 12.20.02					
C	SEE ECN #526 FOR CHANGES	SM 11.21.02	FILE # LEDS2M	DWN: D.D.	APP:	FINAL	
B	CHANGED DIM "A" (SEE ENGINEERING)	SM 11.01.01	MAT'L: SEE NOTES	DT: 05-20-96	DT:		
A	CHANGED FILE NO. AND TITLE BLOCK	SM 10.03.01	RE: RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		PART # SEE TABLE	PRINT TYPE CA
REV	DESCRIPTION	ENGR DATE	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1'				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[LEDS2M-250-01](#) [LEDS2M-160-01](#) [LEDS2M-900-01](#) [LEDS2M-320-01](#) [LEDS2M-650-01](#) [LEDS2M-120-01](#) [LEDS2M-140-01](#) [LEDS2M-850-01](#) [LEDS2M-450-01](#) [LEDS2M-460-01](#) [LEDS2M-500-01](#) [LEDS2M-550-01](#) [LEDS2M-600-01](#) [LEDS2M-750-01](#) [LEDS2M-300-01](#) [LEDS2M-340-01](#) [LEDS2M-360-01](#) [LEDS2M-380-01](#) [LEDS2M-400-01](#) [LEDS2M-440-01](#) [LEDS2M-180-01](#) [LEDS2M-200-01](#) [LEDS2M-220-01](#) [LEDS2M-240-01](#) [LEDS2M-260-01](#) [LEDS2M-280-01](#)