

## Specification Sheet

Part Number: 161-64014

Clips can be linked together and each turning freely, allowing differing cable sizes to be bundled together, organized and protected flexibly and efficiently.

Clips can be easily released and re-used allowing for the Helawrap cables to be mounted securely in an unlimited number of positions.

Fit snugly around the Helawrap cable cover and holding it firmly and to any surface.



Helawrap, Mounting Base without Adhesive, HWBASE, PA66HIRHS, Black, 50/pkg

|                |           |
|----------------|-----------|
| Article Number | 161-64014 |
|----------------|-----------|

|      |        |
|------|--------|
| Type | HWBASE |
|------|--------|

|       |            |
|-------|------------|
| Color | Black (BK) |
|-------|------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                                        |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Clips can be joined to a base and another clip of any size. Different cable sizes can be bundled together, organized and protected flexibly and efficiently. |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                            |
|-------------------|----------------------------------------------------------------------------|
| Short Description | Helawrap, Mounting Base without Adhesive, HWBASE, PA66HIRHS, Black, 50/pkg |
|-------------------|----------------------------------------------------------------------------|

|                              |                                                                  |
|------------------------------|------------------------------------------------------------------|
| Global Part Name             | HWBASE-PA66HIRHS-BK                                              |
| Length L (Imperial)          | 1.5                                                              |
| Length L (Metric)            | 38                                                               |
| Fixation Method              | screw-hole                                                       |
| Width W (Imperial)           | 1.5                                                              |
| Width W (Metric)             | 38                                                               |
| Material                     | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| Material Shortcut            | PA66HIRHS                                                        |
| Flammability                 | UL 94 HB                                                         |
| Halogen Free                 | Yes                                                              |
| UV Resistant (Yes/No)        | No                                                               |
| Use Conditions               | For Indoor and Outdoor Use                                       |
| Operating Temperature        | -40°F to +221°F (-40°C to +105°C)                                |
| Reach Compliant (Article 33) | Yes                                                              |
| ROHS Compliant               | Yes                                                              |

|                             |            |
|-----------------------------|------------|
| Package Quantity (Imperial) | 50         |
| Package Quantity (Metric)   | 50         |
| Customs Number              | 3926909988 |
| Weight (Metric)             | 0.14       |
| Weight (Imperial)           | 0.31       |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)