


Specification Sheet

Part Number: 181-13008



- Strong fingers prevent unwanted breaking.
- Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
- Supplied with mounting holes to streamline installation.
- Optional covers enhance protection and appearance.

Slotted Wall Wiring Duct, 1" x 3", Non-Adhesive, PVC, White, 120ft/Carton

|                     |                                                                                                                                                                                                                                                                                                                                                       |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 181-13008                                                                                                                                                                                                                                                                                                                                             |
| Type                | SL1X3                                                                                                                                                                                                                                                                                                                                                 |
| Color               | White (WH)                                                                                                                                                                                                                                                                                                                                            |
| Quantity Per        | carton                                                                                                                                                                                                                                                                                                                                                |
| Product Description | HellermannTyton Slotted Wall Wiring Duct features break-away fingers that provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and T's. |
| Short Description   | Slotted Wall Wiring Duct, 1" x 3", Non-Adhesive, PVC, White, 120ft/Carton                                                                                                                                                                                                                                                                             |

|                                  |                                                 |
|----------------------------------|-------------------------------------------------|
| Global Part Name                 | SL1X3-PVC-WH                                    |
| Length L (Imperial)              | 6.0                                             |
| Length L (Metric)                | 1.83                                            |
| Fixation Method                  | Non-Adhesive                                    |
| Width W (Imperial)               | 1.0                                             |
| Width W (Metric)                 | 25.4                                            |
| Height H (Imperial)              | 3.07                                            |
| Height H (Metric)                | 77.9                                            |
| Mounting Hole Centers (Imperial) | 4.0                                             |
| Material                         | Polyvinylchloride - rigid extrusion grade (PVC) |
| Material Shortcut                | PVC                                             |
| Halogen Free                     | No                                              |
| UV Resistant (Yes/No)            | No                                              |
| Use Conditions                   | For Indoor Use Only                             |
| Operating Temperature            | +122°F (+50°C)                                  |

|                              |                                                  |
|------------------------------|--------------------------------------------------|
| Reach Compliant (Article 33) | No                                               |
| ROHS Compliant               | Yes                                              |
| Certification/Specification  | UL CSA EN 50085-2-3_1A EN 50085-1:2005 + A1:2013 |
| UL Recognized (US)           | Yes                                              |
| Package Quantity (Imperial)  | 120.0                                            |
| Package Quantity (Metric)    | 36.58                                            |
| Customs Number               | 3925900000                                       |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)