



NYLON 6/6 (RMS-01) COLOR: NATURAL PART NO.	FLAME RET. (RMS-19) COLOR: NATURAL PART NO.	DIM. "A"
MSPS-3-01	MSPS-3-19	3/16 (4.8)
MSPS-4-01	MSPS-4-19	1/4 (6.4)
MSPS-5-01	MSPS-5-19	5/16 (7.9)
MSPS-6-01	MSPS-6-19	3/8 (9.5)
MSPS-7-01	MSPS-7-19	7/16 (11.1)
MSPS-8-01	MSPS-8-19	1/2 (12.7)
MSPS-10-01	MSPS-10-19	5/8 (15.9)
MSPS-11-01	MSPS-11-19	11/16 (17.5)
MSPS-12-01	MSPS-12-19	3/4 (19.1)
MSPS-14-01	MSPS-14-19	7/8 (22.2)

TITLE: MINIATURE SUPPORT POST					DWG IN IN (MM)				
E	SEE CO 200628 FOR CHANGES	SK 02.17.11	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE # MSPS	DWN: P.B.	APP:	FINAL	PART # SEE TABLE	PRINT TYPE CA
D	SEE CO 200053 FOR CHANGES	RG 10.24.07		MAT'L: SEE TABLE	DT: 04-18-94	DT:			
C	SEE ECN #862 FOR CHANGES	SM 10.04.04		RE: RICHCO, INC.			RICHCO INC.		
B	SEE ENC #496 FOR CHANGES	SM 10.23.02		PO BOX 804238,CHICAGO,60680			(773) 539-4060		
A	REMOVED NOTES; ADDED COLUMN "-19" AND "-01 TO P/N; CHANGED FILE NO.	SM 08.15.02							
REV	DESCRIPTION	ENGR DATE							

TOLERANCES
UNLESS NOTED
.XX=±.010
.XXX=±.005
FRAC=±1/64
ANG=±1°

FILE # MSPS
MAT'L: SEE TABLE
RE: RICHCO, INC.

DWN: P.B.
DT: 04-18-94
APP:
DT:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[MSPS-12-01](#) [MSPS-14-01](#) [MSPS-4-01](#) [MSPS-8-01](#) [MSPS-10-01](#) [MSPS-11-01](#) [MSPS-3-01](#) [MSPS-5-01](#) [MSPS-6-01](#) [MSPS-7-01](#)