

Specification Sheet

Part Number: 126-00015



An all-in-one bundling and fixing solution reduces costs.

Disc provides secure insertion and minimizes access of dust, dirt and water.

1-Piece Cable Tie with Arrowhead Mount with Disc for Oval Holes, 6.3"L, 0.24 - 0.48" Hole, PA66HS, Black, 500/pkg

Article Number	126-00015
Type	T50SDOP
Color	Black (BK)
Quantity Per	pack
Product Description	The Domed Push Mount Tie provides a tight, rattle-free installation and acts as a seal to keep out dust and debris. One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution.
Short Description	1-Piece Cable Tie with Arrowhead Mount with Disc for Oval Holes, 6.3"L, 0.24 - 0.48" Hole, PA66HS, Black, 500/pkg
Global Part Name	T50SDOP-PA66HS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	6.3
Length L (Metric)	160.0
Fixation Method	Arrowhead for oval holes
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.2
Width W (Metric)	5.0
Bundle Diameter Min (Imperial)	0.2
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	1.18
Bundle Diameter Max (Metric)	30.0
Thickness T (Imperial)	0.05

Thickness T (Metric)	1.3
Height H (Imperial)	0.36
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.08
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	1.9
Mounting Hole Diameter D (Imperial)	0.24 x 0.48 "
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.48
Mounting Hole Diameter D Max (Metric)	12.2
Disc Diameter (Metric)	22.0
Disc Diameter (Imperial)	0.87
Stud Length Min (Metric)	9.2
Material	Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com