

Specification Sheet

Part Number: 151-00018



Clip includes an internal rib that spans the inside of the bracket to fit securely into the profile of the tubing to prevent lateral movement and slipping of the tubing.

Extended fir tree allows for a wide range of panel thicknesses.

Fir tree design provides low insertion forces and high extraction forces.

Convoluted Tubing Clip, 0.4" Max Bundle Diameter, Panel Thickness .03"-.24", PA66HIRHS, Black, 500/pkg

Article Number 151-00018

Type CTC10FT6LG

Color Black (BK)

Quantity Per pack

Product Description
Convoluted Tube Clips provide a quick and easy method for firmly securing corrugated covered cables and wires to a surface. Applications such as this can be found in a wide variety of industries such as the wire harness, automotive, trucking, and heavy equipment manufacturing industries.

Short Description
Convoluted Tubing Clip, 0.4" Max Bundle Diameter, Panel Thickness .03"-.24", PA66HIRHS, Black, 500/pkg

Global Part Name CTC10FT6LG-PA66HIRHS-BK

Fixation Method	Fir Tree
Variant	Clips
Width W (Imperial)	0.31
Width W (Metric)	8.0
Bundle Diameter Max (Imperial)	0.4
Bundle Diameter Max (Metric)	10.16
Height H (Imperial)	0.85
Height H (Metric)	21.4
Nominal Diameter (Imperial)	0.38
Nominal Diameter (Metric)	10.0
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.75
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.26 - 0.28 "
Mounting Hole Diameter D (Metric)	6.5 - 7.0 mm

Mounting Hole Diameter D Min (Imperial) 0.26

Mounting Hole Diameter D Max (Imperial) 0.28

Mounting Hole Diameter D Max (Metric) 7.0

Disc Diameter (Metric) 16.0

Disc Diameter (Imperial) 0.63

Material Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut PA66HIRHS

Flammability UL 94 HB

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 500

Package Quantity (Metric) 500

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)