

Specification Sheet

Part Number: 151-01317



Easy assembly without the need of a tool.

Disc covers mounting hole and minimizes ingress of dust, dirt and water.

Standard geometry fits common 6.5 mm hole size.

Push Pin, Mounting Hole Dia. 6.5mm, PA66HIRHSUV, Black, 5000/bulk pack

Article Number	151-01317
----------------	-----------

Type	FT6.5Plug
------	-----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Developed especially for the automotive industry in applications including trunks, doors, wheel housings and dash panels.
---------------------	---

Short Description	Push Pin, Mounting Hole Dia. 6.5mm, PA66HIRHSUV, Black, 5000/bulk pack
-------------------	--

Global Part Name	FT6.5Plug-PA66HIRHSUV-BK
------------------	--------------------------

Minimum Tensile Strength (Imperial)	25
Minimum Tensile Strength (Metric)	110
Length L (Imperial)	0.76
Length L (Metric)	18.60
Fixation Method	Fir Tree
Width W (Imperial)	0.62
Width W (Metric)	15.7
Height H (Imperial)	0.48
Height H (Metric)	12.5
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.27 "
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27

Mounting Hole Diameter D Max (Metric)	6.9
Disc Diameter (Metric)	18.6
Disc Diameter (Imperial)	0.73
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)